

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771728

Luminaire Tested: LD6D75BD010-EU6DR7070959040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR7070959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5299.8 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771728
CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P771728

CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	651041
5°	631691
10°	614088
15°	606025
20°	565912
25°	425140
30°	300534
35°	106453
40°	55982
45°	59629
50°	61737
55°	62900
60°	63284
65°	61944
70°	58461
75°	54162
80°	48071
85°	38988

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 63303 cd/sqm



TEST NUMBER: P771728

CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	543.2	10.3
10°-20°	1490.1	28.1
20°-30°	1641.2	31.0
30°-40°	627.0	11.8
40°-50°	296.1	5.6
50°-60°	294.3	5.6
60°-70°	235.6	4.4
70°-80°	135.4	2.6
80°-90°	36.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3674.5	69.3
0°-40°	4301.5	81.2
0°-60°	4892.0	92.3
0°-90°	5299.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5299.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5959	
5°	5760	543
15°	5358	1490
25°	3526	1641
35°	798	627
45°	386	296
55°	330	294
65°	240	236
75°	128	135
85°	31	37
90°	0	



TEST NUMBER: P771728

CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5958.6
2.5°	5896.3
5°	5759.5
7.5°	5645.4
10°	5535.0
12.5°	5441.6
15°	5357.6
17.5°	5154.8
20°	4867.1
22.5°	4246.3
25°	3526.5
27.5°	3069.9
30°	2382.1
32.5°	1538.7
35°	798.1
37.5°	431.1
40°	392.5
42.5°	389.6
45°	385.9
47.5°	377.4
50°	363.2
52.5°	347.2
55°	330.2
57.5°	311.3
60°	289.6
62.5°	265.1
65°	239.6
67.5°	211.3
70°	183.0
72.5°	154.7
75°	128.3
77.5°	100.9
80°	76.4
82.5°	53.8
85°	31.1
87.5°	12.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)