

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771587

Luminaire Tested: LD6D75BD010-EU6DR6070959050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771587  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6070959050-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9570.1 lumens  
Efficiency: N/A  
Efficacy: 132.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P771587

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P771587

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1241825
5°	1272365
10°	1287731
15°	1226744
20°	1081605
25°	874838
30°	591757
35°	296523
40°	48095
45°	47082
50°	48019
55°	48746
60°	50107
65°	51241
70°	52455
75°	53064
80°	51217
85°	42623

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 53064 cd/sqm



TEST NUMBER: P771587

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1108.8	11.6
10°-20°	2999.8	31.3
20°-30°	3227.5	33.7
30°-40°	1402.9	14.7
40°-50°	235.6	2.5
50°-60°	229.1	2.4
60°-70°	196.0	2.0
70°-80°	131.1	1.4
80°-90°	39.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7336.1	76.7
0°-40°	8739.0	91.3
0°-60°	9203.8	96.2
0°-90°	9570.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9570.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11366	
5°	11601	###
15°	10845	3000
25°	7257	3228
35°	2223	1403
45°	305	236
55°	256	229
65°	198	196
75°	126	131
85°	34	39
90°	0	



TEST NUMBER: P771587

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11365.7
2.5°	11685.2
5°	11600.9
7.5°	11627.5
10°	11606.8
12.5°	11367.2
15°	10845.1
17.5°	10143.9
20°	9302.3
22.5°	8401.5
25°	7256.7
27.5°	5804.1
30°	4690.4
32.5°	3615.0
35°	2223.1
37.5°	951.1
40°	337.2
42.5°	310.6
45°	304.7
47.5°	294.3
50°	282.5
52.5°	269.2
55°	255.9
57.5°	242.6
60°	229.3
62.5°	214.5
65°	198.2
67.5°	181.9
70°	164.2
72.5°	145.0
75°	125.7
77.5°	103.5
80°	81.4
82.5°	57.7
85°	34.0
87.5°	11.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)