

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773265

Luminaire Tested: LD6D85BD010-EU6DR7070959030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8112.7 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773265
CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773265

CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	996567
5°	966955
10°	940003
15°	927668
20°	866244
25°	650773
30°	460042
35°	162954
40°	85678
45°	91258
50°	94509
55°	96274
60°	96871
65°	94830
70°	89512
75°	82910
80°	73617
85°	59798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 96917 cd/sqm



TEST NUMBER: P773265

CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	831.6	10.3
10°-20°	2280.9	28.1
20°-30°	2512.1	31.0
30°-40°	959.8	11.8
40°-50°	453.2	5.6
50°-60°	450.6	5.6
60°-70°	360.7	4.4
70°-80°	207.3	2.6
80°-90°	56.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5624.6	69.3
0°-40°	6584.5	81.2
0°-60°	7488.2	92.3
0°-90°	8112.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8112.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9121	
5°	8816	832
15°	8201	2281
25°	5398	2512
35°	1222	960
45°	591	453
55°	505	451
65°	367	361
75°	196	207
85°	48	56
90°	0	



TEST NUMBER: P773265

CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9121.0
2.5°	9025.7
5°	8816.3
7.5°	8641.5
10°	8472.6
12.5°	8329.6
15°	8201.1
17.5°	7890.6
20°	7450.1
22.5°	6499.9
25°	5398.1
27.5°	4699.1
30°	3646.4
32.5°	2355.3
35°	1221.7
37.5°	660.0
40°	600.7
42.5°	596.4
45°	590.6
47.5°	577.6
50°	556.0
52.5°	531.4
55°	505.4
57.5°	476.6
60°	443.3
62.5°	405.8
65°	366.8
67.5°	323.5
70°	280.2
72.5°	236.8
75°	196.4
77.5°	154.5
80°	117.0
82.5°	82.3
85°	47.7
87.5°	18.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)