

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771664

Luminaire Tested: LD6D75BD010-EU6DR6570959050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7963.8 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771664
CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P771664
 CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | | | | | | | | | | | | | | | | | |
| 4 | 97 | 89 | 84 | 79 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | | | | | | | | | | | | | | | | | | |
| 5 | 92 | 83 | 78 | 73 | 90 | 83 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 72 | 77 | 74 | 71 | 69 | | | | | | | | | | | | | | | | | | | |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 65 | | | | | | | | | | | | | | | | | | | |
| 7 | 83 | 73 | 67 | 63 | 81 | 73 | 67 | 63 | 71 | 66 | 62 | 70 | 66 | 62 | 69 | 65 | 62 | 60 | | | | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 62 | 58 | 65 | 61 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 9 | 75 | 65 | 59 | 55 | 74 | 65 | 59 | 55 | 64 | 58 | 55 | 63 | 58 | 55 | 62 | 58 | 54 | 53 | | | | | | | | | | | | | | | | | | | |
| 10 | 71 | 61 | 56 | 52 | 70 | 61 | 55 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 59 | 54 | 51 | 50 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 856714 |
| 5° | 857420 |
| 10° | 887604 |
| 15° | 889073 |
| 20° | 818549 |
| 25° | 697440 |
| 30° | 533911 |
| 35° | 377206 |
| 40° | 222659 |
| 45° | 90393 |
| 50° | 32772 |
| 55° | 18249 |
| 60° | 10467 |
| 65° | 5765 |
| 70° | 6038 |
| 75° | 4686 |
| 80° | 4908 |
| 85° | 4137 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 90393 cd/sqm



TEST NUMBER: P771664

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 755.0 | 9.5 |
| 10°-20° | 2177.9 | 27.3 |
| 20°-30° | 2613.1 | 32.8 |
| 30°-40° | 1756.0 | 22.1 |
| 40°-50° | 525.7 | 6.6 |
| 50°-60° | 92.8 | 1.2 |
| 60°-70° | 26.4 | 0.3 |
| 70°-80° | 12.9 | 0.2 |
| 80°-90° | 4.1 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5546.0 | 69.6 |
| 0°-40° | 7302.0 | 91.7 |
| 0°-60° | 7920.5 | 99.5 |
| 0°-90° | 7963.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 7963.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7841 | |
| 5° | 7818 | 755 |
| 15° | 7860 | 2178 |
| 25° | 5785 | 2613 |
| 35° | 2828 | 1756 |
| 45° | 585 | 526 |
| 55° | 96 | 93 |
| 65° | 22 | 26 |
| 75° | 11 | 13 |
| 85° | 3 | 4 |
| 90° | 0 | |



TEST NUMBER: P771664

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 7841.0 |
| 2.5° | 7874.4 |
| 5° | 7817.6 |
| 7.5° | 7935.7 |
| 10° | 8000.3 |
| 12.5° | 7984.7 |
| 15° | 7859.9 |
| 17.5° | 7554.6 |
| 20° | 7039.9 |
| 22.5° | 6433.7 |
| 25° | 5785.2 |
| 27.5° | 5053.1 |
| 30° | 4231.9 |
| 32.5° | 3487.6 |
| 35° | 2828.0 |
| 37.5° | 2176.1 |
| 40° | 1561.1 |
| 42.5° | 1019.5 |
| 45° | 585.0 |
| 47.5° | 309.8 |
| 50° | 192.8 |
| 52.5° | 133.7 |
| 55° | 95.8 |
| 57.5° | 69.1 |
| 60° | 47.9 |
| 62.5° | 31.2 |
| 65° | 22.3 |
| 67.5° | 20.1 |
| 70° | 18.9 |
| 72.5° | 14.5 |
| 75° | 11.1 |
| 77.5° | 10.0 |
| 80° | 7.8 |
| 82.5° | 5.6 |
| 85° | 3.3 |
| 87.5° | 2.2 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)