

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772890

Luminaire Tested: LD6D85BD010-EU6DR4570959035-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P772890  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D85BD010-EU6DR4570959035-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11210.0 lumens  
Efficiency: N/A  
Efficacy: 127.8 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P772890  
CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P772890

CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95						95													
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90						90													
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85						85													
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81						81													
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77						77													
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73						73													
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69						69													
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66						66													
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63						63													
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60						60													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2164893
5°	2103253
10°	2012244
15°	1841626
20°	1461050
25°	912150
30°	502749
35°	225750
40°	88915
45°	41905
50°	19871
55°	10382
60°	5113
65°	1215
70°	511
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 41905 cd/sqm



TEST NUMBER: P772890

CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1801.8	16.1
10°-20°	4434.5	39.6
20°-30°	3511.7	31.3
30°-40°	1169.4	10.4
40°-50°	232.1	2.1
50°-60°	52.7	0.5
60°-70°	7.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9748.0	87.0
0°-40°	10917.4	97.4
0°-60°	11202.2	99.9
0°-90°	11210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11210.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	19814	
5°	19177	###
15°	16281	4435
25°	7566	3512
35°	1692	1169
45°	271	232
55°	54	53
65°	5	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772890

CATALOG NUMBER: LD6D85BD010-EU6DR4570959035-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	19814.0
2.5°	19684.6
5°	19176.6
7.5°	18757.4
10°	18137.1
12.5°	17311.1
15°	16281.0
17.5°	14731.9
20°	12565.7
22.5°	9984.9
25°	7566.2
27.5°	5540.2
30°	3984.9
32.5°	2710.1
35°	1692.5
37.5°	1003.6
40°	623.4
42.5°	409.9
45°	271.2
47.5°	174.5
50°	116.9
52.5°	77.9
55°	54.5
57.5°	35.8
60°	23.4
62.5°	12.5
65°	4.7
67.5°	1.6
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)