

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771669

Luminaire Tested: LD6D75BD010-EU6DR6570959050-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771669  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6570959050-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8802.2 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771669  
CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P771669

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	466770
5°	465592
10°	465199
15°	450857
20°	410446
25°	357683
30°	297487
35°	235718
40°	170131
45°	107482
50°	56024
55°	29773
60°	15641
65°	8596
70°	3603
75°	3972
80°	2758
85°	2345

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 107482 cd/sqm



TEST NUMBER: P771669

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	755.8	8.6
10°-20°	2069.7	23.5
20°-30°	2529.9	28.7
30°-40°	2052.7	23.3
40°-50°	1022.9	11.6
50°-60°	285.3	3.2
60°-70°	64.8	0.7
70°-80°	16.9	0.2
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5355.3	60.8
0°-40°	7408.0	84.2
0°-60°	8716.2	99.0
0°-90°	8802.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8802.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7992	
5°	7942	756
15°	7457	2070
25°	5550	2530
35°	3306	2053
45°	1301	1023
55°	292	285
65°	62	65
75°	18	17
85°	4	4
90°	0	



TEST NUMBER: P771669

CATALOG NUMBER: LD6D75BD010-EU6DR6570959050-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7992.1
2.5°	7986.3
5°	7941.6
7.5°	7915.8
10°	7844.2
12.5°	7698.5
15°	7456.6
17.5°	7078.4
20°	6603.9
22.5°	6091.9
25°	5550.5
27.5°	4971.5
30°	4411.2
32.5°	3858.1
35°	3306.1
37.5°	2755.3
40°	2231.5
42.5°	1740.5
45°	1301.3
47.5°	906.7
50°	616.6
52.5°	425.2
55°	292.4
57.5°	197.3
60°	133.9
62.5°	92.8
65°	62.2
67.5°	31.7
70°	21.1
72.5°	20.0
75°	17.6
77.5°	11.7
80°	8.2
82.5°	5.9
85°	3.5
87.5°	2.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)