

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773121

Luminaire Tested: LD6D85BD010-EU6DR6070959035-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773121  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D85BD010-EU6DR6070959035-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10948.7 lumens  
Efficiency: N/A  
Efficacy: 124.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P773121  
CATALOG NUMBER: LD6D85BD010-EU6DR6070959035-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P773121

CATALOG NUMBER: LD6D85BD010-EU6DR6070959035-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1420707
5°	1455648
10°	1473233
15°	1403452
20°	1237411
25°	1000855
30°	676993
35°	339246
40°	55027
45°	53865
50°	54937
55°	55776
60°	57318
65°	58635
70°	59994
75°	60705
80°	58579
85°	48766

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 60705 cd/sqm



TEST NUMBER: P773121

CATALOG NUMBER: LD6D85BD010-EU6DR6070959035-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1268.5	11.6
10°-20°	3431.9	31.3
20°-30°	3692.5	33.7
30°-40°	1605.0	14.7
40°-50°	269.6	2.5
50°-60°	262.1	2.4
60°-70°	224.2	2.0
70°-80°	150.0	1.4
80°-90°	44.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8392.9	76.7
0°-40°	9997.9	91.3
0°-60°	10529.6	96.2
0°-90°	10948.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10948.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13003	
5°	13272	###
15°	12407	3432
25°	8302	3692
35°	2543	1605
45°	349	270
55°	293	262
65°	227	224
75°	144	150
85°	39	45
90°	0	



TEST NUMBER: P773121

CATALOG NUMBER: LD6D85BD010-EU6DR6070959035-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	13002.9
2.5°	13368.4
5°	13272.0
7.5°	13302.5
10°	13278.8
12.5°	13004.6
15°	12407.3
17.5°	11605.2
20°	10642.3
22.5°	9611.7
25°	8302.0
27.5°	6640.2
30°	5366.0
32.5°	4135.8
35°	2543.4
37.5°	1088.1
40°	385.8
42.5°	355.4
45°	348.6
47.5°	336.7
50°	323.2
52.5°	308.0
55°	292.8
57.5°	277.5
60°	262.3
62.5°	245.4
65°	226.8
67.5°	208.1
70°	187.8
72.5°	165.8
75°	143.8
77.5°	118.5
80°	93.1
82.5°	66.0
85°	38.9
87.5°	13.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)