

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758998

Luminaire Tested: LD6D08D010-EU6DR200210IC9024-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P758998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR200210IC9024-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 707.9 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758998
CATALOG NUMBER: LD6D08D010-EU6DR200210IC9024-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P758998

CATALOG NUMBER: LD6D08D010-EU6DR200210IC9024-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	94	94		
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	93	92	91	91	91		
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	90	89	88	88	88		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	87	86	85	85	85		
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	84	83	82	81	81		
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	82	81	80	79	79		
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	80	79	78	77	77		
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	78	77	76	75	75		
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	76	75	74	73	73		
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	74	73	72	71	71		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440277
5°	397210
10°	222935
15°	113319
20°	47974
25°	22146
30°	11721
35°	6322
40°	3380
45°	1993
50°	1156
55°	610
60°	393
65°	284
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1993 cd/sqm



TEST NUMBER: P758998

CATALOG NUMBER: LD6D08D010-EU6DR200210IC9024-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.9	40.5
10°-20°	282.5	39.9
20°-30°	92.3	13.0
30°-40°	31.4	4.4
40°-50°	10.5	1.5
50°-60°	3.2	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	661.7	93.5
0°-40°	693.1	97.9
0°-60°	706.8	99.8
0°-90°	707.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4030	
5°	3622	287
15°	1002	282
25°	184	92
35°	47	31
45°	13	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P758998

CATALOG NUMBER: LD6D08D010-EU6DR200210IC9024-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4029.6
0.5°	4029.6
1°	4024.6
1.5°	4014.5
2°	3996.2
2.5°	3971.8
3°	3937.4
3.5°	3889.3
4°	3817.9
4.5°	3731.0
5°	3621.6
5.5°	3477.7
6°	3330.2
6.5°	3161.2
7°	2995.8
7.5°	2802.1
8°	2629.1
8.5°	2455.1
9°	2294.3
9.5°	2146.8
10°	2009.4
12.5°	1442.8
15°	1001.8
17.5°	654.5
20°	412.6
22.5°	267.3
25°	183.7
27.5°	129.2
30°	92.9
32.5°	66.7
35°	47.4
37.5°	33.0
40°	23.7
42.5°	17.2
45°	12.9
47.5°	10.0
50°	6.8
52.5°	4.3
55°	3.2
57.5°	2.5
60°	1.8
62.5°	1.4
65°	1.1



TEST NUMBER: P758998
CATALOG NUMBER: LD6D08D010-EU6DR200210IC9024-6LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.7
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)