

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773132

Luminaire Tested: LD6D85BD010-EU6DR6070959040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6070959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8595.2 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773132
CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P773132

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1115312
5°	1142736
10°	1156537
15°	1101763
20°	971413
25°	785711
30°	531464
35°	266325
40°	43203
45°	42292
50°	43124
55°	43775
60°	44994
65°	46019
70°	47120
75°	47661
80°	45995
85°	38361

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 47661 cd/sqm



TEST NUMBER: P773132

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	995.8	11.6
10°-20°	2694.2	31.3
20°-30°	2898.7	33.7
30°-40°	1260.0	14.7
40°-50°	211.6	2.5
50°-60°	205.8	2.4
60°-70°	176.0	2.0
70°-80°	117.8	1.4
80°-90°	35.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6588.7	76.7
0°-40°	7848.7	91.3
0°-60°	8266.2	96.2
0°-90°	8595.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8595.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10208	
5°	10419	996
15°	9740	2694
25°	6517	2899
35°	1997	1260
45°	274	212
55°	230	206
65°	178	176
75°	113	118
85°	31	35
90°	0	



TEST NUMBER: P773132

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	10207.8
2.5°	10494.8
5°	10419.0
7.5°	10442.9
10°	10424.3
12.5°	10209.1
15°	9740.2
17.5°	9110.5
20°	8354.6
22.5°	7545.6
25°	6517.4
27.5°	5212.8
30°	4212.5
32.5°	3246.7
35°	1996.7
37.5°	854.2
40°	302.9
42.5°	279.0
45°	273.7
47.5°	264.4
50°	253.7
52.5°	241.8
55°	229.8
57.5°	217.9
60°	205.9
62.5°	192.6
65°	178.0
67.5°	163.4
70°	147.5
72.5°	130.2
75°	112.9
77.5°	93.0
80°	73.1
82.5°	51.8
85°	30.6
87.5°	10.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)