

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773134

Luminaire Tested: LD6D85BD010-EU6DR6070959040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6070959040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11460.6 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773134

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P773134

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | | | 93 | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 97 | 94 | 92 | 94 | 92 | 90 | 92 | 90 | 88 | 86 | | | 86 | | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 90 | 86 | 100 | 94 | 89 | 86 | 91 | 88 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | 80 | | | | | | | | | | | | | | | | |
| 4 | 97 | 89 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | | 75 | | | | | | | | | | | | | | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 78 | 74 | 81 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | | | 70 | | | | | | | | | | | | | | | | |
| 6 | 88 | 79 | 73 | 69 | 87 | 78 | 73 | 69 | 77 | 72 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 66 | | | 66 | | | | | | | | | | | | | | | | |
| 7 | 84 | 75 | 69 | 65 | 83 | 74 | 68 | 64 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 63 | 62 | | | 62 | | | | | | | | | | | | | | | | |
| 8 | 80 | 71 | 65 | 61 | 79 | 70 | 65 | 61 | 69 | 64 | 60 | 68 | 64 | 60 | 67 | 63 | 60 | 59 | | | 59 | | | | | | | | | | | | | | | | |
| 9 | 77 | 67 | 61 | 57 | 75 | 67 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 55 | | | 55 | | | | | | | | | | | | | | | | |
| 10 | 73 | 64 | 58 | 54 | 72 | 63 | 58 | 54 | 62 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 53 | | | 53 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1487126 |
| 5° | 1523703 |
| 10° | 1542109 |
| 15° | 1469059 |
| 20° | 1295256 |
| 25° | 1047643 |
| 30° | 708647 |
| 35° | 355105 |
| 40° | 57608 |
| 45° | 56384 |
| 50° | 57504 |
| 55° | 58366 |
| 60° | 60006 |
| 65° | 61376 |
| 70° | 62805 |
| 75° | 63576 |
| 80° | 61285 |
| 85° | 51023 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 63576 cd/sqm



TEST NUMBER: P773134

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1327.8 | 11.6 |
| 10°-20° | 3592.4 | 31.3 |
| 20°-30° | 3865.1 | 33.7 |
| 30°-40° | 1680.1 | 14.7 |
| 40°-50° | 282.2 | 2.5 |
| 50°-60° | 274.4 | 2.4 |
| 60°-70° | 234.7 | 2.0 |
| 70°-80° | 157.0 | 1.4 |
| 80°-90° | 47.0 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 8785.2 | 76.7 |
| 0°-40° | 10465.3 | 91.3 |
| 0°-60° | 11021.9 | 96.2 |
| 0°-90° | 11460.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 11460.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 13611 | |
| 5° | 13892 | ### |
| 15° | 12987 | 3592 |
| 25° | 8690 | 3865 |
| 35° | 2662 | 1680 |
| 45° | 365 | 282 |
| 55° | 306 | 274 |
| 65° | 237 | 235 |
| 75° | 151 | 157 |
| 85° | 41 | 47 |
| 90° | 0 | |



TEST NUMBER: P773134

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 13610.8 |
| 2.5° | 13993.4 |
| 5° | 13892.5 |
| 7.5° | 13924.4 |
| 10° | 13899.6 |
| 12.5° | 13612.6 |
| 15° | 12987.3 |
| 17.5° | 12147.7 |
| 20° | 11139.8 |
| 22.5° | 10061.1 |
| 25° | 8690.1 |
| 27.5° | 6950.7 |
| 30° | 5616.9 |
| 32.5° | 4329.1 |
| 35° | 2662.3 |
| 37.5° | 1139.0 |
| 40° | 403.9 |
| 42.5° | 372.0 |
| 45° | 364.9 |
| 47.5° | 352.5 |
| 50° | 338.3 |
| 52.5° | 322.4 |
| 55° | 306.4 |
| 57.5° | 290.5 |
| 60° | 274.6 |
| 62.5° | 256.8 |
| 65° | 237.4 |
| 67.5° | 217.9 |
| 70° | 196.6 |
| 72.5° | 173.6 |
| 75° | 150.6 |
| 77.5° | 124.0 |
| 80° | 97.4 |
| 82.5° | 69.1 |
| 85° | 40.7 |
| 87.5° | 14.2 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)