

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773215

Luminaire Tested: LD6D85BD010-EU6DR6570959040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6570959040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10039.0 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773215
CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P773215

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	532357
5°	531014
10°	530559
15°	514205
20°	468123
25°	407941
30°	339292
35°	268836
40°	194033
45°	122580
50°	63893
55°	33958
60°	17837
65°	9812
70°	4115
75°	4536
80°	3162
85°	2680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 122580 cd/sqm



TEST NUMBER: P773215

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	862.0	8.6
10°-20°	2360.5	23.5
20°-30°	2885.3	28.7
30°-40°	2341.1	23.3
40°-50°	1166.6	11.6
50°-60°	325.4	3.2
60°-70°	74.0	0.7
70°-80°	19.3	0.2
80°-90°	4.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6107.8	60.8
0°-40°	8448.9	84.2
0°-60°	9940.9	99.0
0°-90°	10039.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10039.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9115	
5°	9058	862
15°	8504	2360
25°	6330	2885
35°	3771	2341
45°	1484	1167
55°	334	325
65°	71	74
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P773215

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9115.1
2.5°	9108.4
5°	9057.5
7.5°	9028.1
10°	8946.3
12.5°	8780.3
15°	8504.3
17.5°	8073.0
20°	7531.9
22.5°	6947.9
25°	6330.4
27.5°	5670.0
30°	5031.1
32.5°	4400.2
35°	3770.6
37.5°	3142.4
40°	2545.0
42.5°	1985.1
45°	1484.1
47.5°	1034.1
50°	703.2
52.5°	484.9
55°	333.5
57.5°	225.0
60°	152.7
62.5°	105.8
65°	71.0
67.5°	36.2
70°	24.1
72.5°	22.8
75°	20.1
77.5°	13.4
80°	9.4
82.5°	6.7
85°	4.0
87.5°	2.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)