

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773289

Luminaire Tested: LD6D85BD010-EU6DR7070959040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10986.4 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773289
CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P773289

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1349578
5°	1309469
10°	1272975
15°	1256267
20°	1173100
25°	881288
30°	622995
35°	220682
40°	116029
45°	123599
50°	127978
55°	130391
60°	131200
65°	128413
70°	121202
75°	112292
80°	99666
85°	80859

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 131243 cd/sqm



TEST NUMBER: P773289

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1126.1	10.3
10°-20°	3088.9	28.1
20°-30°	3402.0	31.0
30°-40°	1299.8	11.8
40°-50°	613.8	5.6
50°-60°	610.2	5.6
60°-70°	488.5	4.4
70°-80°	280.8	2.6
80°-90°	76.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7617.1	69.3
0°-40°	8916.9	81.2
0°-60°	10140.8	92.3
0°-90°	10986.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10986.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12352	
5°	11939	###
15°	11106	3089
25°	7310	3402
35°	1654	1300
45°	800	614
55°	684	610
65°	497	489
75°	266	281
85°	64	76
90°	0	



TEST NUMBER: P773289

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	12351.9
2.5°	12222.8
5°	11939.2
7.5°	11702.6
10°	11473.8
12.5°	11280.2
15°	11106.1
17.5°	10685.6
20°	10089.2
22.5°	8802.4
25°	7310.2
27.5°	6363.7
30°	4938.0
32.5°	3189.7
35°	1654.5
37.5°	893.7
40°	813.5
42.5°	807.7
45°	799.9
47.5°	782.3
50°	752.9
52.5°	719.7
55°	684.5
57.5°	645.4
60°	600.4
62.5°	549.5
65°	496.7
67.5°	438.1
70°	379.4
72.5°	320.7
75°	266.0
77.5°	209.3
80°	158.4
82.5°	111.5
85°	64.5
87.5°	25.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)