

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759646

Luminaire Tested: LD6D08D010-EU6DR600210IC9030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P759646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR600210IC9030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 818.6 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759646

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P759646

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106223
5°	108845
10°	110159
15°	104937
20°	92518
25°	74829
30°	50617
35°	25369
40°	4108
45°	4033
50°	4114
55°	4172
60°	4283
65°	4395
70°	4472
75°	4559
80°	4342
85°	3636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 4559 cd/sqm



TEST NUMBER: P759646

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.8	11.6
10°-20°	256.6	31.3
20°-30°	276.1	33.7
30°-40°	120.0	14.7
40°-50°	20.2	2.5
50°-60°	19.6	2.4
60°-70°	16.8	2.0
70°-80°	11.2	1.4
80°-90°	3.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.5	76.7
0°-40°	747.5	91.3
0°-60°	787.3	96.2
0°-90°	818.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	818.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	972	
5°	992	95
15°	928	257
25°	621	276
35°	190	120
45°	26	20
55°	22	20
65°	17	17
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P759646

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	972.2
2.5°	999.6
5°	992.4
7.5°	994.6
10°	992.9
12.5°	972.4
15°	927.7
17.5°	867.7
20°	795.7
22.5°	718.7
25°	620.7
27.5°	496.5
30°	401.2
32.5°	309.2
35°	190.2
37.5°	81.4
40°	28.8
42.5°	26.6
45°	26.1
47.5°	25.2
50°	24.2
52.5°	23.0
55°	21.9
57.5°	20.7
60°	19.6
62.5°	18.3
65°	17.0
67.5°	15.6
70°	14.0
72.5°	12.4
75°	10.8
77.5°	8.9
80°	6.9
82.5°	4.9
85°	2.9
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)