

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759801

Luminaire Tested: LD6D08D010-EU6DR700210IC9030-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P759801  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D08D010-EU6DR700210IC9030-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 784.8 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P759801  
CATALOG NUMBER: LD6D08D010-EU6DR700210IC9030-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P759801  
 CATALOG NUMBER: LD6D08D010-EU6DR700210IC9030-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	96401
5°	93533
10°	90920
15°	89734
20°	83798
25°	62954
30°	44498
35°	15766
40°	8287
45°	8823
50°	9145
55°	9315
60°	9375
65°	9178
70°	8657
75°	8021
80°	7110
85°	5767

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 9375 cd/sqm



TEST NUMBER: P759801

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9030-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.4	10.2
10°-20°	220.6	28.1
20°-30°	243.0	31.0
30°-40°	92.8	11.8
40°-50°	43.8	5.6
50°-60°	43.6	5.6
60°-70°	34.9	4.4
70°-80°	20.1	2.6
80°-90°	5.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.1	69.3
0°-40°	636.9	81.2
0°-60°	724.4	92.3
0°-90°	784.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	882	
5°	853	80
15°	793	221
25°	522	243
35°	118	93
45°	57	44
55°	49	44
65°	36	35
75°	19	20
85°	5	5
90°	0	



TEST NUMBER: P759801

CATALOG NUMBER: LD6D08D010-EU6DR700210IC9030-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	882.3
2.5°	873.1
5°	852.8
7.5°	835.9
10°	819.5
12.5°	805.7
15°	793.3
17.5°	763.3
20°	720.7
22.5°	628.8
25°	522.2
27.5°	454.6
30°	352.7
32.5°	227.9
35°	118.2
37.5°	63.8
40°	58.1
42.5°	57.7
45°	57.1
47.5°	55.9
50°	53.8
52.5°	51.4
55°	48.9
57.5°	46.1
60°	42.9
62.5°	39.2
65°	35.5
67.5°	31.3
70°	27.1
72.5°	22.9
75°	19.0
77.5°	15.0
80°	11.3
82.5°	8.0
85°	4.6
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)