

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759204

Luminaire Tested: LD6D08D010-EU6DR300210IC9040-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P759204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D08D010-EU6DR300210IC9040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 864.8 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759204

CATALOG NUMBER: LD6D08D010-EU6DR300210IC9040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P759204

CATALOG NUMBER: LD6D08D010-EU6DR300210IC9040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	212852	212852	212852
5°	206734	206496	206742
10°	179061	177802	179022
15°	116829	116203	115616
20°	58094	60277	58013
25°	29264	33006	28664
30°	11720	12763	10208
35°	5438	5205	4364
40°	2348	2608	2208
45°	1656	2057	1667
50°	572	1489	595
55°	334	614	347
60°	230	276	230
65°	145	145	145
70°	90	67	90
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2057 cd/sqm



TEST NUMBER: P759204

CATALOG NUMBER: LD6D08D010-EU6DR300210IC9040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.5	28.3
10°-20°	393.8	45.5
20°-30°	170.2	19.7
30°-40°	38.8	4.5
40°-50°	13.3	1.5
50°-60°	3.3	0.4
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.5	93.5
0°-40°	847.3	98.0
0°-60°	863.9	99.9
0°-90°	864.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2781	2781	2781	2781	2781	
5°	2691	2688	2688	2693	2691	245
15°	1474	1457	1466	1462	1459	395
25°	346	360	391	350	339	166
35°	58	59	56	55	47	39
45°	15	19	19	19	15	11
55°	2	3	5	3	3	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P759204

CATALOG NUMBER: LD6D08D010-EU6DR300210IC9040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2780.8	2780.8	2780.8	2780.8	2780.8
2.5°	2762.3	2760.4	2761.5	2762.9	2763.4
5°	2690.6	2688.1	2687.5	2693.1	2690.7
7.5°	2546.1	2542.4	2536.8	2549.5	2561.4
10°	2303.8	2299.8	2287.6	2293.6	2303.3
12.5°	1946.3	1933.1	1932.8	1951.9	1949.3
15°	1474.3	1456.6	1466.4	1461.7	1459.0
17.5°	991.4	984.6	997.7	993.8	976.7
20°	713.2	715.0	740.0	727.4	712.2
22.5°	520.4	526.8	556.4	524.1	512.2
25°	346.5	359.6	390.8	350.5	339.4
27.5°	213.1	219.1	250.7	210.4	204.4
30°	132.6	129.5	144.4	124.0	115.5
32.5°	87.0	83.1	87.9	78.9	72.1
35°	58.2	59.4	55.7	55.3	46.7
37.5°	36.3	41.8	36.8	39.3	30.0
40°	23.5	30.3	26.1	28.8	22.1
42.5°	19.3	23.3	21.4	22.8	19.7
45°	15.3	19.0	19.0	19.0	15.4
47.5°	8.5	12.7	16.3	12.9	9.0
50°	4.8	6.4	12.5	6.7	5.0
52.5°	3.3	3.7	8.6	3.8	3.4
55°	2.5	2.6	4.6	2.8	2.6
57.5°	1.9	2.1	2.5	2.1	1.9
60°	1.5	1.5	1.8	1.7	1.5
62.5°	1.1	1.1	1.2	1.1	1.1
65°	0.8	0.8	0.8	0.8	0.8
67.5°	0.4	0.6	0.6	0.6	0.6
70°	0.4	0.3	0.3	0.3	0.4
72.5°	0.3	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)