

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774042

Luminaire Tested: LD6D90BD010-EU6DR7070959030-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR7070959030-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6410.7 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P774042
CATALOG NUMBER: LD6D90BD010-EU6DR7070959030-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P774042

CATALOG NUMBER: LD6D90BD010-EU6DR7070959030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	787497
5°	764105
10°	742808
15°	733053
20°	684522
25°	514243
30°	363527
35°	128768
40°	67706
45°	72114
50°	74672
55°	76082
60°	76548
65°	74949
70°	70728
75°	65518
80°	58139
85°	47262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 76582 cd/sqm



TEST NUMBER: P774042

CATALOG NUMBER: LD6D90BD010-EU6DR7070959030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	657.1	10.3
10°-20°	1802.4	28.1
20°-30°	1985.1	31.0
30°-40°	758.5	11.8
40°-50°	358.1	5.6
50°-60°	356.0	5.6
60°-70°	285.1	4.4
70°-80°	163.8	2.6
80°-90°	44.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4444.7	69.3
0°-40°	5203.1	81.2
0°-60°	5917.3	92.3
0°-90°	6410.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6410.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7208	
5°	6967	657
15°	6481	1802
25°	4266	1985
35°	965	758
45°	467	358
55°	399	356
65°	290	285
75°	155	164
85°	38	45
90°	0	



TEST NUMBER: P774042

CATALOG NUMBER: LD6D90BD010-EU6DR7070959030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7207.5
2.5°	7132.2
5°	6966.8
7.5°	6828.7
10°	6695.2
12.5°	6582.2
15°	6480.6
17.5°	6235.3
20°	5887.2
22.5°	5136.3
25°	4265.6
27.5°	3713.3
30°	2881.4
32.5°	1861.2
35°	965.4
37.5°	521.5
40°	474.7
42.5°	471.3
45°	466.7
47.5°	456.5
50°	439.3
52.5°	419.9
55°	399.4
57.5°	376.6
60°	350.3
62.5°	320.7
65°	289.9
67.5°	255.6
70°	221.4
72.5°	187.1
75°	155.2
77.5°	122.1
80°	92.4
82.5°	65.0
85°	37.7
87.5°	14.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)