

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773982

Luminaire Tested: LD6D90BD010-EU6DR6570959035-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773982  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D90BD010-EU6DR6570959035-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10174.3 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P773982  
CATALOG NUMBER: LD6D90BD010-EU6DR6570959035-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P773982

CATALOG NUMBER: LD6D90BD010-EU6DR6570959035-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	539535
5°	538172
10°	537711
15°	521140
20°	474432
25°	413438
30°	343865
35°	272458
40°	196648
45°	124232
50°	64756
55°	34417
60°	18082
65°	9936
70°	4167
75°	4603
80°	3195
85°	2747

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 124232 cd/sqm



TEST NUMBER: P773982

CATALOG NUMBER: LD6D90BD010-EU6DR6570959035-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	873.6	8.6
10°-20°	2392.3	23.5
20°-30°	2924.2	28.7
30°-40°	2372.6	23.3
40°-50°	1182.3	11.6
50°-60°	329.8	3.2
60°-70°	74.9	0.7
70°-80°	19.5	0.2
80°-90°	5.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6190.1	60.8
0°-40°	8562.8	84.2
0°-60°	10074.9	99.0
0°-90°	10174.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10174.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9238	
5°	9180	874
15°	8619	2392
25°	6416	2924
35°	3821	2373
45°	1504	1182
55°	338	330
65°	72	75
75°	20	20
85°	4	5
90°	0	



TEST NUMBER: P773982

CATALOG NUMBER: LD6D90BD010-EU6DR6570959035-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9238.0
2.5°	9231.2
5°	9179.6
7.5°	9149.8
10°	9066.9
12.5°	8898.6
15°	8619.0
17.5°	8181.8
20°	7633.4
22.5°	7041.5
25°	6415.7
27.5°	5746.4
30°	5098.9
32.5°	4459.5
35°	3821.4
37.5°	3184.8
40°	2579.3
42.5°	2011.9
45°	1504.1
47.5°	1048.0
50°	712.7
52.5°	491.4
55°	338.0
57.5°	228.1
60°	154.8
62.5°	107.2
65°	71.9
67.5°	36.7
70°	24.4
72.5°	23.1
75°	20.4
77.5°	13.6
80°	9.5
82.5°	6.8
85°	4.1
87.5°	2.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)