

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771848

Luminaire Tested: LD6D80BD010-EU6DR3070959027-6LBDP1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771848  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D80BD010-EU6DR3070959027-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8172.7 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771848  
CATALOG NUMBER: LD6D80BD010-EU6DR3070959027-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P771848

CATALOG NUMBER: LD6D80BD010-EU6DR3070959027-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2011499	2011499	2011499
5°	1953749	1951475	1953849
10°	1692242	1680312	1691846
15°	1104108	1098173	1092658
20°	549020	569620	548287
25°	276561	311863	270894
30°	110728	120654	96472
35°	51356	49188	41236
40°	22172	24620	20883
45°	15642	19409	15783
50°	5382	14135	5680
55°	3096	5858	3270
60°	2174	2572	2174
65°	1395	1395	1395
70°	873	582	873
75°	0	384	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 19409 cd/sqm



TEST NUMBER: P771848

CATALOG NUMBER: LD6D80BD010-EU6DR3070959027-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2310.9	28.3
10°-20°	3721.7	45.5
20°-30°	1608.2	19.7
30°-40°	366.5	4.5
40°-50°	125.9	1.5
50°-60°	30.7	0.4
60°-70°	8.0	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7640.7	93.5
0°-40°	8007.3	98.0
0°-60°	8163.9	99.9
0°-90°	8172.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8172.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	26279	26279	26279	26279	26279	
5°	25428	25403	25398	25451	25429	2313
15°	13933	13765	13858	13813	13789	3731
25°	3275	3398	3693	3312	3208	1567
35°	550	561	526	522	441	373
45°	144	179	179	179	146	103
55°	23	24	44	26	24	23
65°	8	8	8	8	8	8
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P771848

CATALOG NUMBER: LD6D80BD010-EU6DR3070959027-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	26279.2	26279.2	26279.2	26279.2	26279.2
2.5°	26105.0	26086.9	26097.3	26110.2	26115.3
5°	25427.6	25403.1	25398.0	25450.9	25428.9
7.5°	24061.3	24026.5	23973.6	24093.5	24205.8
10°	21772.4	21733.7	21618.9	21675.7	21767.3
12.5°	18393.4	18268.2	18265.6	18446.3	18421.7
15°	13933.1	13765.3	13858.2	13813.1	13788.6
17.5°	9369.6	9305.1	9428.9	9391.5	9230.2
20°	6740.1	6756.9	6993.0	6874.3	6731.1
22.5°	4918.3	4979.0	5258.9	4953.1	4840.9
25°	3274.6	3398.4	3692.6	3312.0	3207.5
27.5°	2014.0	2070.8	2368.8	1988.2	1931.5
30°	1252.8	1224.4	1365.1	1171.5	1091.5
32.5°	821.9	785.7	830.9	745.7	681.2
35°	549.6	561.2	526.4	522.5	441.3
37.5°	343.2	394.8	348.4	371.6	283.8
40°	221.9	286.4	246.4	272.2	209.0
42.5°	181.9	220.6	202.6	215.5	185.8
45°	144.5	179.3	179.3	179.3	145.8
47.5°	80.0	120.0	153.5	122.6	85.2
50°	45.2	60.6	118.7	63.2	47.7
52.5°	31.0	34.8	81.3	36.1	32.3
55°	23.2	24.5	43.9	25.8	24.5
57.5°	18.1	19.4	23.2	19.4	18.1
60°	14.2	14.2	16.8	15.5	14.2
62.5°	10.3	10.3	11.6	10.3	10.3
65°	7.7	7.7	7.7	7.7	7.7
67.5°	3.9	5.2	5.2	5.2	5.2
70°	3.9	2.6	2.6	2.6	3.9
72.5°	2.6	1.3	1.3	1.3	1.3
75°	0.0	0.0	1.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)