

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773761

Luminaire Tested: LD6D90BD010-EU6DR5070959040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR5070959040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12608.1 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773761

CATALOG NUMBER: LD6D90BD010-EU6DR5070959040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P773761

CATALOG NUMBER: LD6D90BD010-EU6DR5070959040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 102 | 102 | 101 | 99 | 98 | 97 | 97 | 95 | | | | | | | | | | | | | | | | | | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 98 | 95 | 97 | 95 | 93 | 95 | 93 | 91 | 90 | | | | | | | | | | | | | | | | | | | |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | | | | | | | | | | | | | | | | | | | |
| 4 | 100 | 94 | 89 | 85 | 99 | 93 | 88 | 85 | 90 | 87 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 80 | | | | | | | | | | | | | | | | | | | |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 76 | | | | | | | | | | | | | | | | | | | |
| 6 | 92 | 84 | 79 | 75 | 91 | 83 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 74 | 72 | | | | | | | | | | | | | | | | | | | |
| 7 | 88 | 80 | 75 | 71 | 87 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | | | | | | | | | | | | | | | | | | | |
| 8 | 85 | 76 | 71 | 67 | 84 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 65 | | | | | | | | | | | | | | | | | | | |
| 9 | 81 | 73 | 68 | 64 | 80 | 72 | 67 | 64 | 71 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 63 | 62 | | | | | | | | | | | | | | | | | | | |
| 10 | 78 | 70 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 60 | 59 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2219621 |
| 5° | 2196348 |
| 10° | 2160179 |
| 15° | 1967014 |
| 20° | 1636785 |
| 25° | 1161870 |
| 30° | 614984 |
| 35° | 250613 |
| 40° | 93080 |
| 45° | 42616 |
| 50° | 17474 |
| 55° | 9144 |
| 60° | 4502 |
| 65° | 1319 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42616 cd/sqm



TEST NUMBER: P773761

CATALOG NUMBER: LD6D90BD010-EU6DR5070959040-6LBS1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1892.8 | 15.0 |
| 10°-20° | 4783.5 | 37.9 |
| 20°-30° | 4296.9 | 34.1 |
| 30°-40° | 1345.3 | 10.7 |
| 40°-50° | 235.6 | 1.9 |
| 50°-60° | 47.0 | 0.4 |
| 60°-70° | 7.1 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 10973.2 | 87.0 |
| 0°-40° | 12318.5 | 97.7 |
| 0°-60° | 12601.0 | 99.9 |
| 0°-90° | 12608.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 12608.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 20315 | |
| 5° | 20025 | ### |
| 15° | 17390 | 4784 |
| 25° | 9638 | 4297 |
| 35° | 1879 | 1345 |
| 45° | 276 | 236 |
| 55° | 48 | 47 |
| 65° | 5 | 7 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P773761

CATALOG NUMBER: LD6D90BD010-EU6DR5070959040-6LBS1H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 20314.9 |
| 2.5° | 20213.8 |
| 5° | 20025.4 |
| 7.5° | 19737.7 |
| 10° | 19470.5 |
| 12.5° | 18614.1 |
| 15° | 17389.5 |
| 17.5° | 15834.3 |
| 20° | 14077.1 |
| 22.5° | 12044.0 |
| 25° | 9637.6 |
| 27.5° | 7085.6 |
| 30° | 4874.5 |
| 32.5° | 3173.7 |
| 35° | 1878.9 |
| 37.5° | 1079.0 |
| 40° | 652.6 |
| 42.5° | 424.8 |
| 45° | 275.8 |
| 47.5° | 167.8 |
| 50° | 102.8 |
| 52.5° | 70.2 |
| 55° | 48.0 |
| 57.5° | 32.5 |
| 60° | 20.6 |
| 62.5° | 12.0 |
| 65° | 5.1 |
| 67.5° | 1.7 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)