

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773912

Luminaire Tested: LD6D90BD010-EU6DR6070959040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6070959040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9118.2 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773912
CATALOG NUMBER: LD6D90BD010-EU6DR6070959040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P773912

CATALOG NUMBER: LD6D90BD010-EU6DR6070959040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1183196
5°	1212294
10°	1226933
15°	1168818
20°	1030538
25°	833524
30°	563812
35°	282531
40°	45827
45°	44857
50°	45758
55°	46442
60°	47725
65°	48811
70°	49963
75°	50574
80°	48764
85°	40618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 50574 cd/sqm



TEST NUMBER: P773912

CATALOG NUMBER: LD6D90BD010-EU6DR6070959040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1056.4	11.6
10°-20°	2858.2	31.3
20°-30°	3075.1	33.7
30°-40°	1336.7	14.7
40°-50°	224.5	2.5
50°-60°	218.3	2.4
60°-70°	186.7	2.0
70°-80°	124.9	1.4
80°-90°	37.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6989.7	76.7
0°-40°	8326.4	91.3
0°-60°	8769.2	96.2
0°-90°	9118.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9118.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10829	
5°	11053	###
15°	10333	2858
25°	6914	3075
35°	2118	1337
45°	290	225
55°	244	218
65°	189	187
75°	120	125
85°	32	37
90°	0	



TEST NUMBER: P773912

CATALOG NUMBER: LD6D90BD010-EU6DR6070959040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	10829.1
2.5°	11133.5
5°	11053.2
7.5°	11078.5
10°	11058.8
12.5°	10830.5
15°	10333.0
17.5°	9665.0
20°	8863.1
22.5°	8004.8
25°	6914.0
27.5°	5530.1
30°	4468.9
32.5°	3444.3
35°	2118.2
37.5°	906.2
40°	321.3
42.5°	296.0
45°	290.3
47.5°	280.5
50°	269.2
52.5°	256.5
55°	243.8
57.5°	231.1
60°	218.4
62.5°	204.3
65°	188.8
67.5°	173.3
70°	156.4
72.5°	138.1
75°	119.8
77.5°	98.7
80°	77.5
82.5°	55.0
85°	32.4
87.5°	11.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)