

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773993

Luminaire Tested: LD6D90BD010-EU6DR6570959040-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8729.3 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773993
CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773993

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	939052
5°	939821
10°	972910
15°	974520
20°	897208
25°	764469
30°	585234
35°	413460
40°	244054
45°	99077
50°	35917
55°	20001
60°	11472
65°	6308
70°	6645
75°	5150
80°	5348
85°	4638

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 99077 cd/sqm



TEST NUMBER: P773993

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	827.6	9.5
10°-20°	2387.2	27.3
20°-30°	2864.2	32.8
30°-40°	1924.8	22.1
40°-50°	576.2	6.6
50°-60°	101.7	1.2
60°-70°	28.9	0.3
70°-80°	14.2	0.2
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6079.0	69.6
0°-40°	8003.8	91.7
0°-60°	8681.7	99.5
0°-90°	8729.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8729.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8595	
5°	8569	828
15°	8615	2387
25°	6341	2864
35°	3100	1925
45°	641	576
55°	105	102
65°	24	29
75°	12	14
85°	4	4
90°	0	



TEST NUMBER: P773993

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8594.6
2.5°	8631.2
5°	8568.9
7.5°	8698.4
10°	8769.2
12.5°	8752.1
15°	8615.3
17.5°	8280.7
20°	7716.4
22.5°	7052.0
25°	6341.2
27.5°	5538.8
30°	4638.7
32.5°	3822.8
35°	3099.8
37.5°	2385.3
40°	1711.1
42.5°	1117.5
45°	641.2
47.5°	339.5
50°	211.3
52.5°	146.6
55°	105.0
57.5°	75.7
60°	52.5
62.5°	34.2
65°	24.4
67.5°	22.0
70°	20.8
72.5°	15.9
75°	12.2
77.5°	11.0
80°	8.5
82.5°	6.1
85°	3.7
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)