

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773619

Luminaire Tested: LD6D90BD010-EU6DR4070959050-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773619  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D90BD010-EU6DR4070959050-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13417.5 lumens  
Efficiency: N/A  
Efficacy: 135.7 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P773619  
CATALOG NUMBER: LD6D90BD010-EU6DR4070959050-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P773619

CATALOG NUMBER: LD6D90BD010-EU6DR4070959050-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69																			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3413284
5°	3396698
10°	3210619
15°	2729432
20°	1860308
25°	776199
30°	244063
35°	113429
40°	62729
45°	28756
50°	13955
55°	7639
60°	3977
65°	1422
70°	575
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28756 cd/sqm



TEST NUMBER: P773619

CATALOG NUMBER: LD6D90BD010-EU6DR4070959050-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2891.8	21.6
10°-20°	6478.4	48.3
20°-30°	3242.9	24.2
30°-40°	594.4	4.4
40°-50°	164.0	1.2
50°-60°	38.5	0.3
60°-70°	7.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12613.0	94.0
0°-40°	13207.5	98.4
0°-60°	13410.0	99.9
0°-90°	13417.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13417.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	31240	
5°	30970	###
15°	24130	6478
25°	6438	3243
35°	850	594
45°	186	164
55°	40	39
65°	6	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P773619

CATALOG NUMBER: LD6D90BD010-EU6DR4070959050-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	31239.8
2.5°	31194.1
5°	30969.7
7.5°	30254.3
10°	28938.5
12.5°	26887.2
15°	24129.7
17.5°	20543.6
20°	15999.5
22.5°	10907.8
25°	6438.5
27.5°	3403.6
30°	1934.5
32.5°	1250.1
35°	850.4
37.5°	607.7
40°	439.8
42.5°	301.1
45°	186.1
47.5°	118.6
50°	82.1
52.5°	58.4
55°	40.1
57.5°	25.5
60°	18.2
62.5°	10.9
65°	5.5
67.5°	3.6
70°	1.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)