

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774010

Luminaire Tested: LD6D90BD010-EU6DR6570959050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10192.2 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774010

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774010

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	540481
5°	539116
10°	538654
15°	522053
20°	475265
25°	414159
30°	344465
35°	272936
40°	196991
45°	124455
50°	64874
55°	34478
60°	18105
65°	9964
70°	4184
75°	4603
80°	3195
85°	2747

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 124455 cd/sqm



TEST NUMBER: P774010

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	875.2	8.6
10°-20°	2396.5	23.5
20°-30°	2929.3	28.7
30°-40°	2376.8	23.3
40°-50°	1184.4	11.6
50°-60°	330.4	3.2
60°-70°	75.1	0.7
70°-80°	19.5	0.2
80°-90°	5.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6201.0	60.8
0°-40°	8577.8	84.2
0°-60°	10092.6	99.0
0°-90°	10192.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10192.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9254	
5°	9196	875
15°	8634	2397
25°	6427	2929
35°	3828	2377
45°	1507	1184
55°	339	330
65°	72	75
75°	20	20
85°	4	5
90°	0	



TEST NUMBER: P774010

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9254.2
2.5°	9247.4
5°	9195.7
7.5°	9165.8
10°	9082.8
12.5°	8914.2
15°	8634.1
17.5°	8196.2
20°	7646.8
22.5°	7053.9
25°	6426.9
27.5°	5756.5
30°	5107.8
32.5°	4467.3
35°	3828.1
37.5°	3190.4
40°	2583.8
42.5°	2015.4
45°	1506.8
47.5°	1049.9
50°	714.0
52.5°	492.3
55°	338.6
57.5°	228.5
60°	155.0
62.5°	107.4
65°	72.1
67.5°	36.7
70°	24.5
72.5°	23.1
75°	20.4
77.5°	13.6
80°	9.5
82.5°	6.8
85°	4.1
87.5°	2.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)