

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774082

Luminaire Tested: LD6D90BD010-EU6DR7070959050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR7070959050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11738.3 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P774082
CATALOG NUMBER: LD6D90BD010-EU6DR7070959050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P774082

CATALOG NUMBER: LD6D90BD010-EU6DR7070959050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1441936
5°	1399087
10°	1360090
15°	1342246
20°	1253387
25°	941602
30°	665638
35°	235781
40°	123974
45°	132051
50°	136749
55°	139306
60°	140182
65°	137203
70°	129508
75°	119975
80°	106462
85°	86500

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 140211 cd/sqm



TEST NUMBER: P774082

CATALOG NUMBER: LD6D90BD010-EU6DR7070959050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1203.2	10.3
10°-20°	3300.3	28.1
20°-30°	3634.8	31.0
30°-40°	1388.8	11.8
40°-50°	655.8	5.6
50°-60°	651.9	5.6
60°-70°	521.9	4.4
70°-80°	300.0	2.6
80°-90°	81.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8138.4	69.3
0°-40°	9527.1	81.2
0°-60°	10834.8	92.3
0°-90°	11738.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11738.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13197	
5°	12756	###
15°	11866	3300
25°	7810	3635
35°	1768	1389
45°	855	656
55°	731	652
65°	531	522
75°	284	300
85°	69	82
90°	0	



TEST NUMBER: P774082

CATALOG NUMBER: LD6D90BD010-EU6DR7070959050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13197.2
2.5°	13059.3
5°	12756.3
7.5°	12503.5
10°	12259.0
12.5°	12052.2
15°	11866.2
17.5°	11417.0
20°	10779.7
22.5°	9404.8
25°	7810.5
27.5°	6799.2
30°	5276.0
32.5°	3408.0
35°	1767.7
37.5°	954.9
40°	869.2
42.5°	863.0
45°	854.6
47.5°	835.8
50°	804.5
52.5°	768.9
55°	731.3
57.5°	689.5
60°	641.5
62.5°	587.1
65°	530.7
67.5°	468.0
70°	405.4
72.5°	342.7
75°	284.2
77.5°	223.6
80°	169.2
82.5°	119.1
85°	69.0
87.5°	27.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)