

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772422

Luminaire Tested: LD6D80BD010-EU6DR6570959035-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959035-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9008.8 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P772422
CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P772422

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	477732
5°	476526
10°	476123
15°	461444
20°	420086
25°	366080
30°	304474
35°	241251
40°	174126
45°	110001
50°	57342
55°	30476
60°	16003
65°	8803
70°	3688
75°	4062
80°	2825
85°	2412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 110001 cd/sqm



TEST NUMBER: P772422

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	773.6	8.6
10°-20°	2118.3	23.5
20°-30°	2589.3	28.7
30°-40°	2100.9	23.3
40°-50°	1046.9	11.6
50°-60°	292.0	3.2
60°-70°	66.4	0.7
70°-80°	17.2	0.2
80°-90°	4.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5481.1	60.8
0°-40°	7581.9	84.2
0°-60°	8920.8	99.0
0°-90°	9008.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9008.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8180	
5°	8128	774
15°	7632	2118
25°	5681	2589
35°	3384	2101
45°	1332	1047
55°	299	292
65°	64	66
75°	18	17
85°	4	4
90°	0	



TEST NUMBER: P772422

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8179.8
2.5°	8173.8
5°	8128.1
7.5°	8101.7
10°	8028.4
12.5°	7879.3
15°	7631.7
17.5°	7244.6
20°	6759.0
22.5°	6234.9
25°	5680.8
27.5°	5088.2
30°	4514.8
32.5°	3948.7
35°	3383.7
37.5°	2820.0
40°	2283.9
42.5°	1781.4
45°	1331.8
47.5°	928.0
50°	631.1
52.5°	435.1
55°	299.3
57.5°	201.9
60°	137.0
62.5°	95.0
65°	63.7
67.5°	32.5
70°	21.6
72.5°	20.4
75°	18.0
77.5°	12.0
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)