

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772497

Luminaire Tested: LD6D80BD010-EU6DR7070959035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P772497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR7070959035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10352.0 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P772497
CATALOG NUMBER: LD6D80BD010-EU6DR7070959035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P772497

CATALOG NUMBER: LD6D80BD010-EU6DR7070959035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1271642
5°	1233857
10°	1199473
15°	1183726
20°	1105360
25°	830401
30°	587026
35°	207930
40°	109340
45°	116460
50°	120583
55°	122866
60°	123618
65°	121019
70°	114206
75°	105791
80°	93941
85°	76220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 123658 cd/sqm



TEST NUMBER: P772497

CATALOG NUMBER: LD6D80BD010-EU6DR7070959035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1061.1	10.3
10°-20°	2910.5	28.1
20°-30°	3205.6	31.0
30°-40°	1224.8	11.8
40°-50°	578.3	5.6
50°-60°	574.9	5.6
60°-70°	460.3	4.4
70°-80°	264.6	2.6
80°-90°	71.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7177.2	69.3
0°-40°	8402.0	81.2
0°-60°	9555.2	92.3
0°-90°	10352.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10352.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11639	
5°	11250	###
15°	10465	2911
25°	6888	3206
35°	1559	1225
45°	754	578
55°	645	575
65°	468	460
75°	251	265
85°	61	72
90°	0	



TEST NUMBER: P772497

CATALOG NUMBER: LD6D80BD010-EU6DR7070959035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	11638.6
2.5°	11517.0
5°	11249.8
7.5°	11026.9
10°	10811.3
12.5°	10628.8
15°	10464.8
17.5°	10068.6
20°	9506.6
22.5°	8294.1
25°	6888.1
27.5°	5996.2
30°	4652.9
32.5°	3005.5
35°	1558.9
37.5°	842.1
40°	766.6
42.5°	761.0
45°	753.7
47.5°	737.1
50°	709.4
52.5°	678.1
55°	645.0
57.5°	608.1
60°	565.7
62.5°	517.8
65°	468.1
67.5°	412.8
70°	357.5
72.5°	302.2
75°	250.6
77.5°	197.2
80°	149.3
82.5°	105.0
85°	60.8
87.5°	24.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)