

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760640

Luminaire Tested: LD6D10D010-EU6DR600210IC9024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR600210IC9024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 725.6 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760640
CATALOG NUMBER: LD6D10D010-EU6DR600210IC9024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760640

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94161
5°	96473
10°	97644
15°	93015
20°	82007
25°	66330
30°	44864
35°	22488
40°	3651
45°	3569
50°	3638
55°	3696
60°	3802
65°	3878
70°	3961
75°	4010
80°	3901
85°	3259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 4010 cd/sqm



TEST NUMBER: P760640

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	11.6
10°-20°	227.5	31.3
20°-30°	244.7	33.7
30°-40°	106.4	14.7
40°-50°	17.9	2.5
50°-60°	17.4	2.4
60°-70°	14.9	2.0
70°-80°	9.9	1.4
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.2	76.7
0°-40°	662.6	91.3
0°-60°	697.8	96.2
0°-90°	725.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	862	
5°	880	84
15°	822	227
25°	550	245
35°	169	106
45°	23	18
55°	19	17
65°	15	15
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P760640

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	861.8
2.5°	886.0
5°	879.6
7.5°	881.6
10°	880.1
12.5°	861.9
15°	822.3
17.5°	769.1
20°	705.3
22.5°	637.0
25°	550.2
27.5°	440.1
30°	355.6
32.5°	274.1
35°	168.6
37.5°	72.1
40°	25.6
42.5°	23.5
45°	23.1
47.5°	22.3
50°	21.4
52.5°	20.4
55°	19.4
57.5°	18.4
60°	17.4
62.5°	16.3
65°	15.0
67.5°	13.8
70°	12.4
72.5°	11.0
75°	9.5
77.5°	7.8
80°	6.2
82.5°	4.4
85°	2.6
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)