

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760198

Luminaire Tested: LD6D10D010-EU6DR300210IC9030-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR300210IC9030-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 770.7 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760198
CATALOG NUMBER: LD6D10D010-EU6DR300210IC9030-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760198

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9030-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	189697	189697	189697
5°	184252	184037	184260
10°	159591	158464	159552
15°	104118	103563	103040
20°	51773	53720	51708
25°	26080	29408	25548
30°	10438	11375	9104
35°	4850	4635	3887
40°	2088	2328	1968
45°	1472	1829	1494
50°	500	1334	536
55°	294	547	307
60°	199	245	199
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1829 cd/sqm



TEST NUMBER: P760198

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9030-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.9	28.3
10°-20°	351.0	45.5
20°-30°	151.7	19.7
30°-40°	34.6	4.5
40°-50°	11.9	1.5
50°-60°	2.9	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.6	93.5
0°-40°	755.1	98.0
0°-60°	769.9	99.9
0°-90°	770.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2478	2478	2478	2478	2478	
5°	2398	2396	2395	2400	2398	218
15°	1314	1298	1307	1303	1300	352
25°	309	320	348	312	302	148
35°	52	53	50	49	42	35
45°	14	17	17	17	14	10
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P760198

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9030-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2478.3	2478.3	2478.3	2478.3	2478.3
2.5°	2461.9	2460.1	2461.1	2462.3	2462.8
5°	2398.0	2395.7	2395.2	2400.1	2398.1
7.5°	2269.1	2265.8	2260.9	2272.2	2282.8
10°	2053.3	2049.6	2038.8	2044.1	2052.8
12.5°	1734.6	1722.8	1722.6	1739.6	1737.3
15°	1313.9	1298.1	1306.9	1302.7	1300.3
17.5°	883.6	877.5	889.2	885.7	870.5
20°	635.6	637.2	659.5	648.3	634.8
22.5°	463.8	469.5	495.9	467.1	456.5
25°	308.8	320.5	348.2	312.3	302.5
27.5°	189.9	195.3	223.4	187.5	182.1
30°	118.1	115.4	128.7	110.5	103.0
32.5°	77.5	74.1	78.4	70.3	64.2
35°	51.9	52.9	49.6	49.3	41.6
37.5°	32.4	37.2	32.8	35.1	26.8
40°	20.9	27.0	23.3	25.7	19.7
42.5°	17.1	20.8	19.1	20.3	17.5
45°	13.6	16.9	16.9	16.9	13.8
47.5°	7.6	11.3	14.5	11.6	8.0
50°	4.2	5.7	11.2	6.0	4.5
52.5°	2.9	3.3	7.7	3.4	3.0
55°	2.2	2.3	4.1	2.4	2.3
57.5°	1.7	1.8	2.2	1.8	1.7
60°	1.3	1.3	1.6	1.4	1.3
62.5°	1.0	1.0	1.1	1.0	1.0
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)