

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772448

Luminaire Tested: LD6D80BD010-EU6DR6570959050-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P772448  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D80BD010-EU6DR6570959050-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9497.4 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P772448  
CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P772448

CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	503640
5°	502369
10°	501938
15°	486464
20°	442865
25°	385934
30°	320989
35°	254334
40°	183565
45°	115972
50°	60449
55°	32125
60°	16879
65°	9287
70°	3893
75°	4287
80°	2993
85°	2546

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 115972 cd/sqm



TEST NUMBER: P772448

CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	815.5	8.6
10°-20°	2233.1	23.5
20°-30°	2729.7	28.7
30°-40°	2214.8	23.3
40°-50°	1103.7	11.6
50°-60°	307.8	3.2
60°-70°	70.0	0.7
70°-80°	18.2	0.2
80°-90°	4.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5778.3	60.8
0°-40°	7993.1	84.2
0°-60°	9404.6	99.0
0°-90°	9497.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9497.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8623	
5°	8569	815
15°	8046	2233
25°	5989	2730
35°	3567	2215
45°	1404	1104
55°	316	308
65°	67	70
75°	19	18
85°	4	5
90°	0	



TEST NUMBER: P772448

CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8623.4
2.5°	8617.1
5°	8568.9
7.5°	8541.0
10°	8463.7
12.5°	8306.6
15°	8045.5
17.5°	7637.5
20°	7125.5
22.5°	6573.0
25°	5988.9
27.5°	5364.1
30°	4759.7
32.5°	4162.8
35°	3567.2
37.5°	2972.9
40°	2407.7
42.5°	1878.0
45°	1404.1
47.5°	978.3
50°	665.3
52.5°	458.7
55°	315.5
57.5°	212.9
60°	144.5
62.5°	100.1
65°	67.2
67.5°	34.2
70°	22.8
72.5°	21.5
75°	19.0
77.5°	12.7
80°	8.9
82.5°	6.3
85°	3.8
87.5°	2.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)