

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760666

Luminaire Tested: LD6D10D010-EU6DR600210IC9030-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR600210IC9030-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 831.7 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760666
CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760666

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107928
5°	110577
10°	111912
15°	106611
20°	93995
25°	76023
30°	51437
35°	25770
40°	4179
45°	4095
50°	4181
55°	4229
60°	4349
65°	4447
70°	4568
75°	4601
80°	4404
85°	3761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 4601 cd/sqm



TEST NUMBER: P760666

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	11.6
10°-20°	260.7	31.3
20°-30°	280.5	33.7
30°-40°	121.9	14.7
40°-50°	20.5	2.5
50°-60°	19.9	2.4
60°-70°	17.0	2.0
70°-80°	11.4	1.4
80°-90°	3.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	637.6	76.7
0°-40°	759.5	91.3
0°-60°	799.9	96.2
0°-90°	831.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	831.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	988	
5°	1008	96
15°	942	261
25°	631	280
35°	193	122
45°	26	20
55°	22	20
65°	17	17
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P760666

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	987.8
2.5°	1015.6
5°	1008.2
7.5°	1010.5
10°	1008.7
12.5°	987.9
15°	942.5
17.5°	881.6
20°	808.4
22.5°	730.2
25°	630.6
27.5°	504.4
30°	407.7
32.5°	314.1
35°	193.2
37.5°	82.7
40°	29.3
42.5°	27.0
45°	26.5
47.5°	25.6
50°	24.6
52.5°	23.4
55°	22.2
57.5°	21.1
60°	19.9
62.5°	18.6
65°	17.2
67.5°	15.8
70°	14.3
72.5°	12.6
75°	10.9
77.5°	9.0
80°	7.0
82.5°	5.0
85°	3.0
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)