

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772523

Luminaire Tested: LD6D80BD010-EU6DR7070959050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P772523  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D80BD010-EU6DR7070959050-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10913.4 lumens  
Efficiency: N/A  
Efficacy: 138.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P772523  
CATALOG NUMBER: LD6D80BD010-EU6DR7070959050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P772523

CATALOG NUMBER: LD6D80BD010-EU6DR7070959050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1340608
5°	1300771
10°	1264510
15°	1247919
20°	1165298
25°	875429
30°	618857
35°	219215
40°	115259
45°	122765
50°	127128
55°	129514
60°	130326
65°	127560
70°	120403
75°	111532
80°	99037
85°	80357

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 130369 cd/sqm



TEST NUMBER: P772523

CATALOG NUMBER: LD6D80BD010-EU6DR7070959050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1118.6	10.3
10°-20°	3068.4	28.1
20°-30°	3379.4	31.0
30°-40°	1291.2	11.8
40°-50°	609.7	5.6
50°-60°	606.1	5.6
60°-70°	485.3	4.4
70°-80°	278.9	2.6
80°-90°	75.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7566.4	69.3
0°-40°	8857.6	81.2
0°-60°	10073.4	92.3
0°-90°	10913.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10913.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12270	
5°	11860	###
15°	11032	3068
25°	7262	3379
35°	1644	1291
45°	794	610
55°	680	606
65°	493	485
75°	264	279
85°	64	76
90°	0	



TEST NUMBER: P772523

CATALOG NUMBER: LD6D80BD010-EU6DR7070959050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12269.8
2.5°	12141.6
5°	11859.9
7.5°	11624.8
10°	11397.5
12.5°	11205.2
15°	11032.3
17.5°	10614.7
20°	10022.1
22.5°	8743.9
25°	7261.6
27.5°	6321.4
30°	4905.2
32.5°	3168.5
35°	1643.5
37.5°	887.8
40°	808.1
42.5°	802.3
45°	794.5
47.5°	777.1
50°	747.9
52.5°	714.9
55°	679.9
57.5°	641.1
60°	596.4
62.5°	545.9
65°	493.4
67.5°	435.2
70°	376.9
72.5°	318.6
75°	264.2
77.5°	207.9
80°	157.4
82.5°	110.7
85°	64.1
87.5°	25.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)