

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773173

Luminaire Tested: LD6D85BD010-EU6DR6570959027-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6570959027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9189.3 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773173
CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P773173

CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	988526
5°	989340
10°	1024178
15°	1025874
20°	944484
25°	804747
30°	616069
35°	435241
40°	256919
45°	104300
50°	37803
55°	21068
60°	12084
65°	6644
70°	6996
75°	5446
80°	5663
85°	4889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 104300 cd/sqm



TEST NUMBER: P773173

CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	871.2	9.5
10°-20°	2513.0	27.3
20°-30°	3015.1	32.8
30°-40°	2026.3	22.1
40°-50°	606.6	6.6
50°-60°	107.1	1.2
60°-70°	30.4	0.3
70°-80°	14.9	0.2
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6399.3	69.6
0°-40°	8425.5	91.7
0°-60°	9139.2	99.5
0°-90°	9189.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9189.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9047	
5°	9020	871
15°	9069	2513
25°	6675	3015
35°	3263	2026
45°	675	607
55°	111	107
65°	26	30
75°	13	15
85°	4	5
90°	0	



TEST NUMBER: P773173

CATALOG NUMBER: LD6D85BD010-EU6DR6570959027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	9047.4
2.5°	9086.0
5°	9020.4
7.5°	9156.7
10°	9231.3
12.5°	9213.3
15°	9069.3
17.5°	8717.0
20°	8123.0
22.5°	7423.6
25°	6675.3
27.5°	5830.6
30°	4883.1
32.5°	4024.2
35°	3263.1
37.5°	2511.0
40°	1801.3
42.5°	1176.4
45°	675.0
47.5°	357.4
50°	222.4
52.5°	154.3
55°	110.6
57.5°	79.7
60°	55.3
62.5°	36.0
65°	25.7
67.5°	23.1
70°	21.9
72.5°	16.7
75°	12.9
77.5°	11.6
80°	9.0
82.5°	6.4
85°	3.9
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)