

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773135

Luminaire Tested: LD6D85BD010-EU6DR6070959040-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6070959040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9884.5 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773135
CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773135
 CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1282634
5°	1314174
10°	1330046
15°	1267047
20°	1117150
25°	903579
30°	611199
35°	306273
40°	49678
45°	48627
50°	49600
55°	50347
60°	51746
65°	52922
70°	54180
75°	54837
80°	52853
85°	44002

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 54837 cd/sqm



TEST NUMBER: P773135

CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1145.2	11.6
10°-20°	3098.4	31.3
20°-30°	3333.6	33.7
30°-40°	1449.0	14.7
40°-50°	243.4	2.5
50°-60°	236.6	2.4
60°-70°	202.4	2.0
70°-80°	135.4	1.4
80°-90°	40.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7577.2	76.7
0°-40°	9026.2	91.3
0°-60°	9506.2	96.2
0°-90°	9884.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9884.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11739	
5°	11982	###
15°	11201	3098
25°	7495	3334
35°	2296	1449
45°	315	243
55°	264	237
65°	205	202
75°	130	135
85°	35	40
90°	0	



TEST NUMBER: P773135
CATALOG NUMBER: LD6D85BD010-EU6DR6070959040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	11739.2
2.5°	12069.2
5°	11982.1
7.5°	12009.6
10°	11988.2
12.5°	11740.7
15°	11201.4
17.5°	10477.2
20°	9608.0
22.5°	8677.6
25°	7495.1
27.5°	5994.9
30°	4844.5
32.5°	3733.8
35°	2296.2
37.5°	982.3
40°	348.3
42.5°	320.8
45°	314.7
47.5°	304.0
50°	291.8
52.5°	278.0
55°	264.3
57.5°	250.5
60°	236.8
62.5°	221.5
65°	204.7
67.5°	187.9
70°	169.6
72.5°	149.7
75°	129.9
77.5°	106.9
80°	84.0
82.5°	59.6
85°	35.1
87.5°	12.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)