

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760549

Luminaire Tested: LD6D10D010-EU6DR500210IC9050-6LBSQW1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760549  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR500210IC9050-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1008.5 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760549  
CATALOG NUMBER: LD6D10D010-EU6DR500210IC9050-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P760549

CATALOG NUMBER: LD6D10D010-EU6DR500210IC9050-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95																												
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																												
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85																												
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																												
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76																												
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72																												
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69																												
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																												
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																												
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	177538
5°	175682
10°	172788
15°	157343
20°	130923
25°	92937
30°	49191
35°	20047
40°	7445
45°	3415
50°	1394
55°	724
60°	371
65°	103
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3415 cd/sqm



TEST NUMBER: P760549

CATALOG NUMBER: LD6D10D010-EU6DR500210IC9050-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.4	15.0
10°-20°	382.6	37.9
20°-30°	343.7	34.1
30°-40°	107.6	10.7
40°-50°	18.8	1.9
50°-60°	3.7	0.4
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	877.7	87.0
0°-40°	985.4	97.7
0°-60°	1008.0	99.9
0°-90°	1008.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1625	
5°	1602	151
15°	1391	383
25°	771	344
35°	150	108
45°	22	19
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760549

CATALOG NUMBER: LD6D10D010-EU6DR500210IC9050-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1624.9
2.5°	1616.9
5°	1601.8
7.5°	1578.8
10°	1557.4
12.5°	1488.9
15°	1391.0
17.5°	1266.6
20°	1126.0
22.5°	963.4
25°	770.9
27.5°	566.8
30°	389.9
32.5°	253.9
35°	150.3
37.5°	86.3
40°	52.2
42.5°	34.0
45°	22.1
47.5°	13.4
50°	8.2
52.5°	5.6
55°	3.8
57.5°	2.6
60°	1.7
62.5°	1.0
65°	0.4
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)