

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760861

Luminaire Tested: LD6D10D010-EU6DR700210IC9050-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR700210IC9050-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 694.7 lumens  
Efficiency: N/A  
Efficacy: 59.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760861  
CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P760861  
 CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	85344
5°	82807
10°	80503
15°	79441
20°	74182
25°	55733
30°	39401
35°	13952
40°	7345
45°	7819
50°	8091
55°	8248
60°	8304
65°	8118
70°	7667
75°	7092
80°	6292
85°	5140

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 8304 cd/sqm



TEST NUMBER: P760861

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.2	10.3
10°-20°	195.3	28.1
20°-30°	215.1	31.0
30°-40°	82.2	11.8
40°-50°	38.8	5.6
50°-60°	38.6	5.6
60°-70°	30.9	4.4
70°-80°	17.7	2.6
80°-90°	4.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.7	69.3
0°-40°	563.9	81.2
0°-60°	641.2	92.3
0°-90°	694.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	694.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	781	
5°	755	71
15°	702	195
25°	462	215
35°	105	82
45°	51	39
55°	43	39
65°	31	31
75°	17	18
85°	4	5
90°	0	



TEST NUMBER: P760861

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9050-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	781.1
2.5°	772.9
5°	755.0
7.5°	740.0
10°	725.6
12.5°	713.3
15°	702.3
17.5°	675.7
20°	638.0
22.5°	556.6
25°	462.3
27.5°	402.4
30°	312.3
32.5°	201.7
35°	104.6
37.5°	56.5
40°	51.5
42.5°	51.0
45°	50.6
47.5°	49.4
50°	47.6
52.5°	45.5
55°	43.3
57.5°	40.8
60°	38.0
62.5°	34.8
65°	31.4
67.5°	27.7
70°	24.0
72.5°	20.3
75°	16.8
77.5°	13.2
80°	10.0
82.5°	7.0
85°	4.1
87.5°	1.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)