

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772840

Luminaire Tested: LD6D85BD010-EU6DR4070959050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR4070959050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11443.1 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P772840

CATALOG NUMBER: LD6D85BD010-EU6DR4070959050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P772840

CATALOG NUMBER: LD6D85BD010-EU6DR4070959050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						96													
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						92													
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						88													
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						84													
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						81													
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						77													
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						74													
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						72													
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						69													
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						67													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2910969
5°	2896829
10°	2738132
15°	2327761
20°	1586532
25°	661972
30°	208144
35°	96743
40°	53500
45°	24537
50°	11899
55°	6515
60°	3409
65°	1215
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24537 cd/sqm



TEST NUMBER: P772840

CATALOG NUMBER: LD6D85BD010-EU6DR4070959050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2466.2	21.6
10°-20°	5525.0	48.3
20°-30°	2765.6	24.2
30°-40°	507.0	4.4
40°-50°	139.9	1.2
50°-60°	32.9	0.3
60°-70°	6.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10756.9	94.0
0°-40°	11263.8	98.4
0°-60°	11436.6	99.9
0°-90°	11443.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11443.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26642	
5°	26412	###
15°	20579	5525
25°	5491	2766
35°	725	507
45°	159	140
55°	34	33
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772840

CATALOG NUMBER: LD6D85BD010-EU6DR4070959050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	26642.4
2.5°	26603.5
5°	26412.1
7.5°	25802.0
10°	24679.8
12.5°	22930.4
15°	20578.7
17.5°	17520.4
20°	13644.9
22.5°	9302.6
25°	5491.0
27.5°	2902.7
30°	1649.8
32.5°	1066.1
35°	725.3
37.5°	518.3
40°	375.1
42.5°	256.8
45°	158.8
47.5°	101.2
50°	70.0
52.5°	49.8
55°	34.2
57.5°	21.8
60°	15.6
62.5°	9.3
65°	4.7
67.5°	3.1
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)