

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761782

Luminaire Tested: LD6D15D010-EU6DR700215IC9024-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761782  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR700215IC9024-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 759.8 lumens  
Efficiency: N/A  
Efficacy: 48.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761782  
CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P761782

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93320
5°	90550
10°	88025
15°	86872
20°	81124
25°	60941
30°	43085
35°	15259
40°	8030
45°	8545
50°	8856
55°	9010
60°	9069
65°	8894
70°	8370
75°	7768
80°	6858
85°	5641

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 9069 cd/sqm



TEST NUMBER: P761782

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.9	10.2
10°-20°	213.6	28.1
20°-30°	235.2	31.0
30°-40°	89.9	11.8
40°-50°	42.5	5.6
50°-60°	42.2	5.6
60°-70°	33.8	4.4
70°-80°	19.4	2.6
80°-90°	5.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.7	69.3
0°-40°	616.6	81.2
0°-60°	701.3	92.3
0°-90°	759.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	854	
5°	826	78
15°	768	214
25°	506	235
35°	114	90
45°	55	42
55°	47	42
65°	34	34
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P761782

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	854.1
2.5°	845.2
5°	825.6
7.5°	809.2
10°	793.4
12.5°	780.0
15°	768.0
17.5°	738.9
20°	697.7
22.5°	608.7
25°	505.5
27.5°	440.0
30°	341.5
32.5°	220.6
35°	114.4
37.5°	61.8
40°	56.3
42.5°	55.9
45°	55.3
47.5°	54.1
50°	52.1
52.5°	49.8
55°	47.3
57.5°	44.6
60°	41.5
62.5°	38.0
65°	34.4
67.5°	30.3
70°	26.2
72.5°	22.2
75°	18.4
77.5°	14.5
80°	10.9
82.5°	7.7
85°	4.5
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)