

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761484

Luminaire Tested: LD6D15D010-EU6DR500215IC9027-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR500215IC9027-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1354.9 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761484
CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P761484

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95	95	93	91	88	86	85	85	83	82	82	80																									
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	88	86	85	85	83	82	80	77	76	74	72																										
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	83	82	80	77	76	74	72																												
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	77	76	74	72																																
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76	74	72																																		
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72																																				
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69																																				
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																																				
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																																				
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238505
5°	236005
10°	232122
15°	211367
20°	175874
25°	124848
30°	66084
35°	26930
40°	9998
45°	4574
50°	1887
55°	991
60°	481
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4574 cd/sqm



TEST NUMBER: P761484

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.4	15.0
10°-20°	514.0	37.9
20°-30°	461.7	34.1
30°-40°	144.6	10.7
40°-50°	25.3	1.9
50°-60°	5.1	0.4
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1179.1	87.0
0°-40°	1323.7	97.7
0°-60°	1354.1	99.9
0°-90°	1354.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1354.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2183	
5°	2152	203
15°	1869	514
25°	1036	462
35°	202	145
45°	30	25
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761484

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2182.9
2.5°	2172.1
5°	2151.8
7.5°	2120.9
10°	2092.2
12.5°	2000.2
15°	1868.6
17.5°	1701.4
20°	1512.6
22.5°	1294.2
25°	1035.6
27.5°	761.4
30°	523.8
32.5°	341.0
35°	201.9
37.5°	116.0
40°	70.1
42.5°	45.7
45°	29.6
47.5°	18.0
50°	11.1
52.5°	7.6
55°	5.2
57.5°	3.5
60°	2.2
62.5°	1.3
65°	0.6
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)