

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761722

Luminaire Tested: LD6D15D010-EU6DR650215IC9027-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761722  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR650215IC9027-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1066.2 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761722  
CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P761722

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114702
5°	114789
10°	118835
15°	119031
20°	109587
25°	93371
30°	71484
35°	50499
40°	29810
45°	12099
50°	4385
55°	2438
60°	1399
65°	776
70°	799
75°	633
80°	629
85°	627

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12099 cd/sqm



TEST NUMBER: P761722

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.1	9.5
10°-20°	291.6	27.3
20°-30°	349.8	32.8
30°-40°	235.1	22.1
40°-50°	70.4	6.6
50°-60°	12.4	1.2
60°-70°	3.5	0.3
70°-80°	1.7	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	742.5	69.6
0°-40°	977.6	91.7
0°-60°	1060.4	99.5
0°-90°	1066.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1066.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1050	
5°	1047	101
15°	1052	292
25°	774	350
35°	379	235
45°	78	70
55°	13	12
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P761722

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1049.8
2.5°	1054.2
5°	1046.6
7.5°	1062.4
10°	1071.1
12.5°	1069.0
15°	1052.3
17.5°	1011.4
20°	942.5
22.5°	861.4
25°	774.5
27.5°	676.5
30°	566.6
32.5°	466.9
35°	378.6
37.5°	291.3
40°	209.0
42.5°	136.5
45°	78.3
47.5°	41.5
50°	25.8
52.5°	17.9
55°	12.8
57.5°	9.2
60°	6.4
62.5°	4.2
65°	3.0
67.5°	2.7
70°	2.5
72.5°	1.9
75°	1.5
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)