

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773399

Luminaire Tested: LD6D90BD010-EU6DR3070959024-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773399  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D90BD010-EU6DR3070959024-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9139.3 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P773399

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P773399

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2249404	2249404	2249404
5°	2184833	2182282	2184941
10°	1892398	1879053	1891947
15°	1234694	1228061	1221888
20°	613957	636992	613134
25°	309270	348745	302928
30°	123827	134919	107882
35°	57430	55009	46104
40°	24800	27538	23351
45°	17493	21715	17645
50°	6014	15802	6359
55°	3470	6552	3657
60°	2434	2878	2434
65°	1576	1576	1576
70°	962	649	962
75°	0	414	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 21715 cd/sqm



TEST NUMBER: P773399

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2584.2	28.3
10°-20°	4161.8	45.5
20°-30°	1798.4	19.7
30°-40°	409.9	4.5
40°-50°	140.8	1.5
50°-60°	34.4	0.4
60°-70°	8.9	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8544.4	93.5
0°-40°	8954.3	98.0
0°-60°	9129.5	99.9
0°-90°	9139.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9139.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	29387	29387	29387	29387	29387	
5°	28435	28408	28402	28461	28436	2586
15°	15581	15393	15497	15447	15419	4172
25°	3662	3800	4129	3704	3587	1753
35°	615	628	589	584	493	417
45°	162	201	201	201	163	115
55°	26	27	49	29	27	25
65°	9	9	9	9	9	9
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P773399

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	29387.3	29387.3	29387.3	29387.3	29387.3
2.5°	29192.5	29172.3	29183.9	29198.3	29204.1
5°	28435.1	28407.7	28401.9	28461.0	28436.5
7.5°	26907.1	26868.2	26809.0	26943.2	27068.7
10°	24347.6	24304.3	24175.9	24239.4	24341.8
12.5°	20568.8	20428.9	20426.0	20628.0	20600.6
15°	15581.0	15393.4	15497.3	15446.8	15419.4
17.5°	10477.7	10405.6	10544.1	10502.3	10321.9
20°	7537.3	7556.0	7820.1	7687.3	7527.2
22.5°	5500.0	5567.8	5880.9	5539.0	5413.5
25°	3661.9	3800.4	4129.3	3703.7	3586.8
27.5°	2252.2	2315.7	2649.0	2223.4	2159.9
30°	1401.0	1369.2	1526.5	1310.1	1220.6
32.5°	919.1	878.7	929.2	833.9	761.8
35°	614.6	627.6	588.7	584.3	493.4
37.5°	383.8	441.5	389.6	415.5	317.4
40°	248.2	320.3	275.6	304.4	233.7
42.5°	203.4	246.7	226.5	241.0	207.8
45°	161.6	200.6	200.6	200.6	163.0
47.5°	89.5	134.2	171.7	137.1	95.2
50°	50.5	67.8	132.7	70.7	53.4
52.5°	34.6	39.0	90.9	40.4	36.1
55°	26.0	27.4	49.1	28.9	27.4
57.5°	20.2	21.6	26.0	21.6	20.2
60°	15.9	15.9	18.8	17.3	15.9
62.5°	11.5	11.5	13.0	11.5	11.5
65°	8.7	8.7	8.7	8.7	8.7
67.5°	4.3	5.8	5.8	5.8	5.8
70°	4.3	2.9	2.9	2.9	4.3
72.5°	2.9	1.4	1.4	1.4	1.4
75°	0.0	0.0	1.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)