

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761795

Luminaire Tested: LD6D15D010-EU6DR700215IC9027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 843.2 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761795
CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761795

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103590
5°	100520
10°	97710
15°	96431
20°	90053
25°	67644
30°	47829
35°	16940
40°	8914
45°	9487
50°	9825
55°	10001
60°	10074
65°	9850
70°	9296
75°	8612
80°	7613
85°	6143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 10086 cd/sqm



TEST NUMBER: P761795

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.4	10.3
10°-20°	237.1	28.1
20°-30°	261.1	31.0
30°-40°	99.8	11.8
40°-50°	47.1	5.6
50°-60°	46.8	5.6
60°-70°	37.5	4.4
70°-80°	21.5	2.6
80°-90°	5.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.7	69.3
0°-40°	684.5	81.2
0°-60°	778.4	92.3
0°-90°	843.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	948	
5°	916	86
15°	852	237
25°	561	261
35°	127	100
45°	61	47
55°	52	47
65°	38	37
75°	20	22
85°	5	6
90°	0	



TEST NUMBER: P761795
CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	948.1
2.5°	938.2
5°	916.5
7.5°	898.3
10°	880.7
12.5°	865.9
15°	852.5
17.5°	820.2
20°	774.5
22.5°	675.7
25°	561.1
27.5°	488.5
30°	379.1
32.5°	244.8
35°	127.0
37.5°	68.6
40°	62.5
42.5°	62.0
45°	61.4
47.5°	60.0
50°	57.8
52.5°	55.2
55°	52.5
57.5°	49.6
60°	46.1
62.5°	42.2
65°	38.1
67.5°	33.6
70°	29.1
72.5°	24.6
75°	20.4
77.5°	16.0
80°	12.1
82.5°	8.5
85°	4.9
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)