

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761661

Luminaire Tested: LD6D15D010-EU6DR600215IC9030-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761661  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR600215IC9030-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1258.9 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761661  
CATALOG NUMBER: LD6D15D010-EU6DR600215IC9030-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P761661

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9030-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	163356
5°	167380
10°	169404
15°	161370
20°	142283
25°	115083
30°	77843
35°	39001
40°	6318
45°	6196
50°	6323
55°	6420
60°	6577
65°	6748
70°	6900
75°	7008
80°	6733
85°	5641

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 7008 cd/sqm



TEST NUMBER: P761661

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9030-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.9	11.6
10°-20°	394.6	31.3
20°-30°	424.6	33.7
30°-40°	184.5	14.7
40°-50°	31.0	2.5
50°-60°	30.1	2.4
60°-70°	25.8	2.0
70°-80°	17.3	1.4
80°-90°	5.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	965.0	76.7
0°-40°	1149.6	91.3
0°-60°	1210.7	96.2
0°-90°	1258.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1258.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1495	
5°	1526	146
15°	1427	395
25°	955	425
35°	292	185
45°	40	31
55°	34	30
65°	26	26
75°	17	17
85°	4	5
90°	0	



TEST NUMBER: P761661

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9030-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1495.1
2.5°	1537.2
5°	1526.1
7.5°	1529.6
10°	1526.9
12.5°	1495.3
15°	1426.6
17.5°	1334.4
20°	1223.7
22.5°	1105.2
25°	954.6
27.5°	763.5
30°	617.0
32.5°	475.5
35°	292.4
37.5°	125.1
40°	44.3
42.5°	40.9
45°	40.1
47.5°	38.7
50°	37.2
52.5°	35.4
55°	33.7
57.5°	31.9
60°	30.1
62.5°	28.2
65°	26.1
67.5°	23.9
70°	21.6
72.5°	19.1
75°	16.6
77.5°	13.6
80°	10.7
82.5°	7.6
85°	4.5
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)