

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P736054

Luminaire Tested: LD6D15D010-EU6DR700215IC9035-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P736054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9035-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1224.2 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P736054

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P736054

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59266
5°	57504
10°	55900
15°	55165
20°	51514
25°	38699
30°	27359
35°	9692
40°	5092
45°	5431
50°	5620
55°	5727
60°	5761
65°	5634
70°	5325
75°	4924
80°	4364
85°	3557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 5762 cd/sqm



TEST NUMBER: P736054

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.5	10.3
10°-20°	344.2	28.1
20°-30°	379.1	31.0
30°-40°	144.9	11.8
40°-50°	68.4	5.6
50°-60°	68.0	5.6
60°-70°	54.4	4.4
70°-80°	31.3	2.6
80°-90°	8.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.8	69.3
0°-40°	993.7	81.2
0°-60°	1130.1	92.3
0°-90°	1224.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1224.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1376	
5°	1330	125
15°	1238	344
25°	815	379
35°	184	145
45°	89	68
55°	76	68
65°	55	54
75°	30	31
85°	7	8
90°	0	



TEST NUMBER: P736054

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1376.5
2.5°	1362.1
5°	1330.5
7.5°	1304.1
10°	1278.6
12.5°	1257.1
15°	1237.6
17.5°	1190.8
20°	1124.3
22.5°	980.9
25°	814.6
27.5°	709.1
30°	550.3
32.5°	355.5
35°	184.4
37.5°	99.6
40°	90.6
42.5°	90.0
45°	89.2
47.5°	87.1
50°	83.9
52.5°	80.2
55°	76.3
57.5°	71.9
60°	66.9
62.5°	61.2
65°	55.3
67.5°	48.8
70°	42.3
72.5°	35.8
75°	29.6
77.5°	23.3
80°	17.6
82.5°	12.4
85°	7.2
87.5°	2.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)