

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773958

Luminaire Tested: LD6D90BD010-EU6DR6570959027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9286.5 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773958

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773958

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	492456
5°	491212
10°	490789
15°	475659
20°	433032
25°	377357
30°	313854
35°	248687
40°	179486
45°	113395
50°	59105
55°	31413
60°	16505
65°	9079
70°	3808
75°	4197
80°	2926
85°	2479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 113395 cd/sqm



TEST NUMBER: P773958

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	797.4	8.6
10°-20°	2183.5	23.5
20°-30°	2669.0	28.7
30°-40°	2165.6	23.3
40°-50°	1079.2	11.6
50°-60°	301.0	3.2
60°-70°	68.4	0.7
70°-80°	17.8	0.2
80°-90°	4.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5650.0	60.8
0°-40°	7815.6	84.2
0°-60°	9195.7	99.0
0°-90°	9286.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9286.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8432	
5°	8379	797
15°	7867	2184
25°	5856	2669
35°	3488	2166
45°	1373	1079
55°	308	301
65°	66	68
75°	19	18
85°	4	5
90°	0	



TEST NUMBER: P773958

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8431.9
2.5°	8425.7
5°	8378.6
7.5°	8351.3
10°	8275.7
12.5°	8122.1
15°	7866.8
17.5°	7467.9
20°	6967.3
22.5°	6427.0
25°	5855.8
27.5°	5245.0
30°	4653.9
32.5°	4070.3
35°	3488.0
37.5°	2906.9
40°	2354.2
42.5°	1836.3
45°	1372.9
47.5°	956.6
50°	650.5
52.5°	448.5
55°	308.5
57.5°	208.2
60°	141.3
62.5°	97.9
65°	65.7
67.5°	33.5
70°	22.3
72.5°	21.1
75°	18.6
77.5°	12.4
80°	8.7
82.5°	6.2
85°	3.7
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)