

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761381

Luminaire Tested: LD6D15D010-EU6DR400215IC9040-6LBSQW1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761381  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR400215IC9040-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1433.8 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761381

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9040-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P761381

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9040-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69																			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	364745
5°	362980
10°	343090
15°	291667
20°	198792
25°	82942
30°	26078
35°	12124
40°	6704
45°	3075
50°	1496
55°	819
60°	415
65°	155
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3075 cd/sqm



TEST NUMBER: P761381

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9040-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	309.0	21.6
10°-20°	692.3	48.3
20°-30°	346.5	24.2
30°-40°	63.5	4.4
40°-50°	17.5	1.2
50°-60°	4.1	0.3
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1347.8	94.0
0°-40°	1411.4	98.4
0°-60°	1433.0	99.9
0°-90°	1433.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1433.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3338	
5°	3310	309
15°	2578	692
25°	688	347
35°	91	64
45°	20	18
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761381

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9040-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3338.3
2.5°	3333.4
5°	3309.5
7.5°	3233.0
10°	3092.4
12.5°	2873.2
15°	2578.5
17.5°	2195.3
20°	1709.7
22.5°	1165.6
25°	688.0
27.5°	363.7
30°	206.7
32.5°	133.6
35°	90.9
37.5°	64.9
40°	47.0
42.5°	32.2
45°	19.9
47.5°	12.7
50°	8.8
52.5°	6.2
55°	4.3
57.5°	2.8
60°	1.9
62.5°	1.1
65°	0.6
67.5°	0.4
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)