

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773969

Luminaire Tested: LD6D90BD010-EU6DR6570959030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10068.2 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773969
CATALOG NUMBER: LD6D90BD010-EU6DR6570959030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P773969

CATALOG NUMBER: LD6D90BD010-EU6DR6570959030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	533911
5°	532561
10°	532107
15°	515705
20°	469485
25°	409126
30°	340277
35°	269620
40°	194597
45°	122943
50°	64084
55°	34060
60°	17883
65°	9840
70°	4132
75°	4558
80°	3162
85°	2680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 122943 cd/sqm



TEST NUMBER: P773969

CATALOG NUMBER: LD6D90BD010-EU6DR6570959030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	864.5	8.6
10°-20°	2367.4	23.5
20°-30°	2893.7	28.7
30°-40°	2347.9	23.3
40°-50°	1170.0	11.6
50°-60°	326.3	3.2
60°-70°	74.2	0.7
70°-80°	19.3	0.2
80°-90°	4.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6125.6	60.8
0°-40°	8473.5	84.2
0°-60°	9969.9	99.0
0°-90°	10068.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10068.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9142	
5°	9084	865
15°	8529	2367
25°	6349	2894
35°	3782	2348
45°	1488	1170
55°	334	326
65°	71	74
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P773969

CATALOG NUMBER: LD6D90BD010-EU6DR6570959030-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9141.7
2.5°	9135.0
5°	9083.9
7.5°	9054.4
10°	8972.4
12.5°	8805.9
15°	8529.1
17.5°	8096.5
20°	7553.8
22.5°	6968.1
25°	6348.8
27.5°	5686.5
30°	5045.7
32.5°	4413.0
35°	3781.6
37.5°	3151.6
40°	2552.4
42.5°	1990.9
45°	1488.5
47.5°	1037.1
50°	705.3
52.5°	486.3
55°	334.5
57.5°	225.7
60°	153.1
62.5°	106.1
65°	71.2
67.5°	36.3
70°	24.2
72.5°	22.8
75°	20.2
77.5°	13.4
80°	9.4
82.5°	6.7
85°	4.0
87.5°	2.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)