

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773992

Luminaire Tested: LD6D90BD010-EU6DR6570959040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773992  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D90BD010-EU6DR6570959040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10623.4 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P773992

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P773992

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1142802
5°	1143745
10°	1184019
15°	1185977
20°	1091884
25°	930342
30°	712218
35°	503173
40°	297012
45°	120570
50°	43702
55°	24345
60°	13964
65°	7678
70°	8082
75°	6290
80°	6544
85°	5641

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 120570 cd/sqm



TEST NUMBER: P773992

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1007.2	9.5
10°-20°	2905.2	27.3
20°-30°	3485.7	32.8
30°-40°	2342.5	22.1
40°-50°	701.2	6.6
50°-60°	123.8	1.2
60°-70°	35.2	0.3
70°-80°	17.3	0.2
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7398.0	69.6
0°-40°	9740.5	91.7
0°-60°	10565.5	99.5
0°-90°	10623.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10623.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10459	
5°	10428	###
15°	10485	2905
25°	7717	3486
35°	3772	2342
45°	780	701
55°	128	124
65°	30	35
75°	15	17
85°	4	5
90°	0	



TEST NUMBER: P773992

CATALOG NUMBER: LD6D90BD010-EU6DR6570959040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10459.4
2.5°	10504.0
5°	10428.2
7.5°	10585.8
10°	10672.0
12.5°	10651.2
15°	10484.7
17.5°	10077.4
20°	9390.7
22.5°	8582.2
25°	7717.1
27.5°	6740.6
30°	5645.2
32.5°	4652.3
35°	3772.4
37.5°	2902.8
40°	2082.4
42.5°	1360.0
45°	780.3
47.5°	413.2
50°	257.1
52.5°	178.4
55°	127.8
57.5°	92.2
60°	63.9
62.5°	41.6
65°	29.7
67.5°	26.8
70°	25.3
72.5°	19.3
75°	14.9
77.5°	13.4
80°	10.4
82.5°	7.4
85°	4.5
87.5°	3.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)