

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756909

Luminaire Tested: LD6D02D010-EU6DR150210IC9027-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P756909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR150210IC9027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 306.4 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P756909

CATALOG NUMBER: LD6D02D010-EU6DR150210IC9027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P756909

CATALOG NUMBER: LD6D02D010-EU6DR150210IC9027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	469760	469760	469760
5°	276055	272477	274632
10°	82391	82969	84238
15°	20490	20889	20246
20°	6129	7102	6259
25°	2158	2750	2189
30°	794	1048	809
35°	399	450	385
40°	249	277	249
45°	189	196	189
50°	146	146	146
55°	125	125	125
60°	98	98	98
65°	79	79	79
70°	66	66	66
75°	38	38	53
80°	32	32	32
85°	17	17	17

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 196 cd/sqm



TEST NUMBER: P756909

CATALOG NUMBER: LD6D02D010-EU6DR150210IC9027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.7	64.9
10°-20°	81.7	26.7
20°-30°	16.2	5.3
30°-40°	4.0	1.3
40°-50°	2.1	0.7
50°-60°	1.6	0.5
60°-70°	1.1	0.4
70°-80°	0.6	0.2
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	296.7	96.8
0°-40°	300.8	98.1
0°-60°	304.5	99.4
0°-90°	306.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	306.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4175	4175	4175	4175	4175	
5°	2716	2688	2681	2700	2702	198
15°	236	240	240	236	233	81
25°	28	32	35	31	28	15
35°	6	6	6	6	5	4
45°	3	3	3	3	3	2
55°	2	2	2	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P756909

CATALOG NUMBER: LD6D02D010-EU6DR150210IC9027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4174.9	4174.9	4174.9	4174.9	4174.9
2.5°	3765.9	3769.1	3770.3	3774.0	3787.8
5°	2716.3	2688.3	2681.1	2699.6	2702.3
7.5°	1609.0	1614.7	1635.3	1639.9	1623.3
10°	883.0	890.2	889.2	895.5	902.8
12.5°	451.6	445.9	444.1	451.4	441.3
15°	235.9	240.4	240.5	236.3	233.1
17.5°	126.9	132.0	140.5	133.6	123.0
20°	74.9	79.5	86.8	81.1	76.5
22.5°	46.3	50.0	55.1	50.7	47.0
25°	27.7	31.5	35.3	31.3	28.1
27.5°	16.4	19.6	22.1	19.4	16.3
30°	10.6	12.4	14.0	12.2	10.8
32.5°	7.4	8.1	8.8	8.1	7.4
35°	5.5	5.8	6.2	5.8	5.3
37.5°	4.2	4.6	4.8	4.4	4.1
40°	3.5	3.7	3.9	3.7	3.5
42.5°	3.0	3.2	3.2	3.2	3.0
45°	2.7	2.7	2.8	2.7	2.7
47.5°	2.3	2.3	2.5	2.3	2.3
50°	2.1	2.1	2.1	2.1	2.1
52.5°	1.9	1.9	1.9	1.9	1.9
55°	1.8	1.8	1.8	1.8	1.8
57.5°	1.6	1.6	1.6	1.6	1.6
60°	1.4	1.4	1.4	1.4	1.4
62.5°	1.2	1.2	1.2	1.2	1.2
65°	1.1	1.1	1.1	1.1	1.1
67.5°	1.1	1.1	1.1	1.1	1.1
70°	0.9	0.9	0.9	0.9	0.9
72.5°	0.7	0.7	0.7	0.7	0.7
75°	0.5	0.5	0.5	0.5	0.7
77.5°	0.5	0.5	0.5	0.5	0.5
80°	0.4	0.4	0.4	0.4	0.4
82.5°	0.4	0.4	0.4	0.4	0.4
85°	0.2	0.2	0.2	0.2	0.2
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)