

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757768

Luminaire Tested: LD6D02D010-EU6DR700210IC9027-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P757768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR700210IC9027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 291.5 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757768
CATALOG NUMBER: LD6D02D010-EU6DR700210IC9027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757768

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35805
5°	34746
10°	33772
15°	33335
20°	31126
25°	23376
30°	16527
35°	5856
40°	3081
45°	3276
50°	3400
55°	3467
60°	3474
65°	3413
70°	3227
75°	2955
80°	2643
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 3477 cd/sqm



TEST NUMBER: P757768

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.9	10.3
10°-20°	82.0	28.1
20°-30°	90.2	31.0
30°-40°	34.5	11.8
40°-50°	16.3	5.6
50°-60°	16.2	5.6
60°-70°	13.0	4.4
70°-80°	7.4	2.6
80°-90°	2.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.1	69.3
0°-40°	236.6	81.2
0°-60°	269.0	92.3
0°-90°	291.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	328	
5°	317	30
15°	295	82
25°	194	90
35°	44	34
45°	21	16
55°	18	16
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P757768

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	327.7
2.5°	324.3
5°	316.8
7.5°	310.5
10°	304.4
12.5°	299.3
15°	294.7
17.5°	283.5
20°	267.7
22.5°	233.5
25°	193.9
27.5°	168.8
30°	131.0
32.5°	84.6
35°	43.9
37.5°	23.7
40°	21.6
42.5°	21.4
45°	21.2
47.5°	20.7
50°	20.0
52.5°	19.1
55°	18.2
57.5°	17.1
60°	15.9
62.5°	14.6
65°	13.2
67.5°	11.6
70°	10.1
72.5°	8.5
75°	7.0
77.5°	5.6
80°	4.2
82.5°	3.0
85°	1.7
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)