

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759938

Luminaire Tested: LD6D10D010-EU6DR150210IC9024-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P759938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR150210IC9024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 791.5 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P759938
CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P759938

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1213449	1213449	1213449
5°	713079	703851	709421
10°	212825	214309	217593
15°	52939	53964	52305
20°	15841	18345	16176
25°	5585	7112	5656
30°	2052	2703	2082
35°	1031	1162	995
40°	646	710	646
45°	476	511	476
50°	382	382	382
55°	320	320	320
60°	260	260	260
65°	193	193	193
70°	168	168	168
75°	106	106	136
80°	71	71	71
85°	42	42	42

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 511 cd/sqm



TEST NUMBER: P759938

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	513.4	64.9
10°-20°	211.2	26.7
20°-30°	41.9	5.3
30°-40°	10.5	1.3
40°-50°	5.5	0.7
50°-60°	4.1	0.5
60°-70°	2.9	0.4
70°-80°	1.6	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	766.5	96.8
0°-40°	776.9	98.2
0°-60°	786.5	99.4
0°-90°	791.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	10784	10784	10784	10784	10784	
5°	7016	6944	6926	6974	6980	512
15°	610	621	621	610	602	209
25°	72	81	91	81	73	38
35°	14	15	16	15	14	10
45°	7	7	7	7	7	5
55°	5	5	5	5	5	4
65°	3	3	3	3	3	3
75°	1	1	1	1	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P759938

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	10784.3	10784.3	10784.3	10784.3	10784.3
2.5°	9727.9	9736.1	9739.3	9748.9	9784.5
5°	7016.5	6944.4	6925.7	6973.6	6980.5
7.5°	4156.3	4170.9	4224.3	4236.2	4193.3
10°	2280.9	2299.6	2296.8	2313.3	2332.0
12.5°	1166.5	1151.8	1147.3	1166.0	1140.0
15°	609.5	620.9	621.3	610.4	602.2
17.5°	327.8	341.0	362.9	345.1	317.8
20°	193.6	205.4	224.2	209.6	197.7
22.5°	119.6	129.2	142.4	131.0	121.4
25°	71.7	81.3	91.3	80.8	72.6
27.5°	42.5	50.7	57.1	50.2	42.0
30°	27.4	32.0	36.1	31.5	27.8
32.5°	19.2	21.0	22.8	21.0	19.2
35°	14.2	15.1	16.0	15.1	13.7
37.5°	11.0	11.9	12.3	11.4	10.5
40°	9.1	9.6	10.0	9.6	9.1
42.5°	7.8	8.2	8.2	8.2	7.8
45°	6.8	6.8	7.3	6.8	6.8
47.5°	5.9	5.9	6.4	5.9	5.9
50°	5.5	5.5	5.5	5.5	5.5
52.5°	5.0	5.0	5.0	5.0	5.0
55°	4.6	4.6	4.6	4.6	4.6
57.5°	4.1	4.1	4.1	4.1	4.1
60°	3.7	3.7	3.7	3.7	3.7
62.5°	3.2	3.2	3.2	3.2	3.2
65°	2.7	2.7	2.7	2.7	2.7
67.5°	2.7	2.7	2.7	2.7	2.7
70°	2.3	2.3	2.3	2.3	2.3
72.5°	1.8	1.8	1.8	1.8	1.8
75°	1.4	1.4	1.4	1.4	1.8
77.5°	1.4	1.4	1.4	1.4	1.4
80°	0.9	0.9	0.9	0.9	0.9
82.5°	0.9	0.9	0.9	0.9	0.9
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)